









## Connectors according to DIN 41612/IEC 60603-2

### Type C

Female connector



No. of contacts	Contact arrangement	Press-fit technology – Performance level II		
		Termination length		
				
		Part number		
32		104-60014-xx	104-65015-xx	104-65016-xx
48		104-60044-xx	104-65045-xx	104-65046-xx
64		304-60054-02	304-65055-03	304-65056-04
96		304-60064-02	304-65065-03	304-65066-04

**Note**  
– \* Rear mating zone Ni, Au

**Options**  
– Without flange  
– Contact arrangement (see page 162)

**Cross reference**  
– Type C with switching function (see page 155)  
– VMEx (see page 152)  
– Type C with IDC (see page 157)

#### Accessories

- Press-fit tool (see page 208)
- Support tool (see page 209)
- Coding accessories (see page 160)
- Shroud (see page 158)

#### On request

- Performance levels I + III or customer-specific
- Special contact length
- Alternative surface Sn, e.g. for WireWrap

#### Ordering note

- Only for 104
- PCB 1.5 to 2.0 mm = xxx-xxxx-01 termination length = 3.2 mm
  - PCB 2.0 to 2.8 mm = xxx-xxxx-02 termination length = 4.6 mm
  - PCB > 2.8 mm = xxx-xxxx-03 termination length = 4.6 mm