

Interface module - VIP-3/SC/D37SUB/M/HW/C300 - 2900675

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



VARIOFACE module, with screw connection and male D-Subminiature pin strip, for mounting on NS 35 rails, 37-pos.

Product Features

- These VARIOFACE modules are used in combination with the relevant front adapters



Key commercial data

package_quantity	1
GTIN	4046356535564

Technical data

Dimensions

Width	88 mm
Height	69 mm
Depth	62 mm

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

General

Nominal voltage U_N	24 V DC
Max. current carrying capacity per branch	2 A
Number of positions	37
Status display	No
Mounting position	Any
Standards/regulations	DIN EN 50178

Connection data for connection 1

Connection name	PCB connection
Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²

Interface module - VIP-3/SC/D37SUB/M/HW/C300 - 2900675

Technical data

Connection data for connection 1

Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Stripping length	8 mm
Screw thread	M 3

Connection data for connection 2

Connection name	D-SUB connection
Number of connections	1
Connection method	D-SUB pin strip
Number of positions	37

Supported controller

Control	HONEYWELL C300
- suitable I/O card	TAIX01 (non-redundant)
- suitable I/O card	TAIX11 (redundant)

classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27250313
eCl@ss 5.1	27250313
eCl@ss 6.0	27242608
eCl@ss 7.0	27242608
eCl@ss 8.0	27242608

ETIM

ETIM 2.0	EC001434
ETIM 3.0	EC001604
ETIM 4.0	EC001604
ETIM 5.0	EC001604

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121421

Interface module - VIP-3/SC/D37SUB/M/HW/C300 - 2900675

approvals

UL Recognized / cUL Recognized / cULus Recognized /

Approval details

UL Recognized	
Nominal voltage UN	125 V
Nominal current IN	2 A
mm ² /AWG/kcmil	30-12


cUL Recognized	
Nominal voltage UN	125 V
Nominal current IN	2 A
mm ² /AWG/kcmil	30-12

cULus Recognized	
-------------------------	--

Drawings

Interface module - VIP-3/SC/D37SUB/M/HW/C300 - 2900675

Circuit diagram



Connection scheme VIP-3/SC/D37SUB/M/HW/C300

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>