

dryfit® block batteries

Sonnenschein GF-V Range (dryfit® traction block)

The GF-V block battery range is designed for hard industrial use. This includes applications such as cleaning machines, pallet trucks, automatic guided vehicles, mobile elevating work platforms, electric cars and buses.

Main technical features and benefits:



- > Battery technology: VRLA (valve regulated lead-acid)
- > Maintenance-free (no topping up during the whole service life)
- > Very high intrinsic safety
- > Robust, safe and reliable
- > Low self-discharge rate
- > 700 cycles in accordance with IEC 60254-1
- > Product range:
 - 6 V and 12 V block batteries
 - 50 Ah up to 240 Ah (C₅)
 - 55 Ah up to 270 Ah (C₂₀)



Technical characteristics and data

Type	Nominal voltage V	Nominal capacity C ₅ (30 °C) Ah	Nominal capacity C ₂₀ (30 °C) Ah	Length (l) max. mm	Width (b/w) max. mm	Height (h) max. mm	Weight kg	Terminal	Terminal position
GF 06 160 V1	6	160	196	246	192	275	29.0	A-Terminal	1
GF 06 160 V2	6	160	196	264	183	270	33.0	A-Terminal	1
GF 06 180 V	6	180	200	246	192	275	31.0	A-Terminal	1
GF 06 180 V Q	6	180	200	246	192	284	31.5	F-M10	1
GF 06 240 V	6	240	270	311	183	358	47.0	A-Terminal	1
GF 12 050 V	12	50.0	55.0	278	175	190	19.0	A-Terminal	3
GF 12 050 V G	12	50.0	55.0	278	175	190	19.0	G-M6	3
GF 12 076 V	12	76	86	330	171	236	28.8	A-Terminal	2
GF 12 090 V	12	90	98	513	189	219	36.5	A-Terminal	4
GF 12 105 V	12	105	120	345	174	283	37.5	A-Terminal	3
GF 12 110 V	12	110	120	513	223	219	45.5	A-Terminal	4
GF 12 160 V	12	160	196	518	274	238	62.5	A-Terminal	4

Drawings with terminal position, terminal and torque



Specifications

Nominal capacity
50 - 240 Ah (C₅)
55 - 270 Ah (C₂₀)

Block battery

Grid plate

700 cycles in accordance with IEC 60254-1

Recyclable

Valve regulated lead-acid batteries

Proof against deep discharge

Maintenance-free (no topping up)

