

## Warning label - WS UT 6 - 3047345

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Warning sign for UT terminal blocks

The illustration shows the product version WS UT 2,5

### Product Features

- Can be isolated lengthwise and crosswise
- Accidental actuation of the terminal points is prevented
- Warning labels and warning covers serve to cover and identify mains terminal blocks
- The warning labels snap into the screw shafts of the relevant terminal block

### Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4046356072823

### Technical data

#### Dimensions

<b>Length (b)</b>	25.2 mm
<b>Height</b>	1 mm
<b>Width (a)</b>	8.2 mm

#### Ambient conditions

<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
<b>Ambient temperature (operation)</b>	-40 °C ... 125 °C

#### General

<b>Color</b>	yellow
<b>Design</b>	Rectangle
<b>Components</b>	free from silicone and halogen
<b>Inflammability class according to UL 94</b>	V0
<b>Material</b>	PA
<b>Printing</b>	Lightning flash
<b>Test for substances that would hinder coating with paint or varnish</b>	VW PV 3.10.7:2005-02
<b>Result</b>	Test passed
<b>Test specification weathering-resistance</b>	Following ISO 4892-2:2013-03
<b>Test duration</b>	96 h

## Warning label - WS UT 6 - 3047345

### Technical data

#### General

<b>Wipe resistance test result</b>	Test passed
<b>Salt spray test specification</b>	DIN EN 60068-2-11:2000-02
<b>Salt spray testing result</b>	Test passed
<b>Alternating condensation climate with SO2 test specification</b>	DIN 50018:1997-06
<b>Climate level</b>	KFW 1.0 S
<b>Cycles</b>	2
<b>Condensation test result</b>	Test passed
<b>Wipe resistance of test specification inscriptions</b>	DIN EN 61010-1 (VDE 0411-1):2011-07
<b>Result</b>	Test passed

### classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	24190218
<b>eCl@ss 4.1</b>	24190218
<b>eCl@ss 5.0</b>	27141137
<b>eCl@ss 5.1</b>	27141137
<b>eCl@ss 6.0</b>	27141137
<b>eCl@ss 7.0</b>	27141137
<b>eCl@ss 8.0</b>	27141137

#### ETIM

<b>ETIM 2.0</b>	EC000761
<b>ETIM 3.0</b>	EC000761
<b>ETIM 4.0</b>	EC000761
<b>ETIM 5.0</b>	EC001777

#### UNSPSC

<b>UNSPSC 6.01</b>	30211811
<b>UNSPSC 7.0901</b>	39121410
<b>UNSPSC 11</b>	39121410
<b>UNSPSC 12.01</b>	39121410
<b>UNSPSC 13.2</b>	39121410

### Drawings