

Marker for terminal blocks - US-TM 100 - 0829255

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Marker for terminal blocks, Card, white, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, Mounting type: Snap into universal marker groove, Lettering field: 104 x 9.8 mm

Product Features

- ✓ The markers, which are supplied as uniform cards, can be labeled quickly, easily, and precisely using the THERMOMARK CARD
- ✓ The cards provide space for including function texts
- ✓ Labeling service: Phoenix Contact can custom-label all UniSheet markers according to your requirements
- ✓ The perforated marking strips are easy to separate and can be easily fitted
- ✓ The US-TM 100 UniSheet markers are suitable for products with universal marker grooves

Key commercial data

package_quantity	10
GTIN	4046356559584

Technical data

Dimensions

Length (b)	9.8 mm
Height	0.5 mm
Width (a)	104 mm

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-30 °C ... 80 °C
Recommended storage conditions	10-30 °C / 40-70 % relative humidity. Storage in poly bags is recommended prior to processing.

General

Color	white
Components	Silicone-free
Inflammability class according to UL 94	V0
Material	PVC
Material	PVC
Number of individual labels	13
Number of individual labels per row	1
Printability	Thermal transfer

Marker for terminal blocks - US-TM 100 - 0829255

Technical data

General

Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed

classifications

eCl@ss

eCl@ss 4.0	24190208
eCl@ss 4.1	24190208
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Magazine

Marker for terminal blocks - US-TM 100 - 0829255

accessories

THERMOMARK CARD-US-MAG1 - 5146451



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>