


## Printed-circuit board connector - FMC 1,5/ 8-ST-3,5 - 1952322

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plug component, Nominal current: 8 A, Rated voltage (III/2): 160 V, Number of positions: 8, Pitch: 3.5 mm, Connection method: Spring-cage conn., Color: green, Contact surface: Tin

The figure shows a 10-position version of the product

### Product Features

- ✓ User-friendly actuation of the terminal point using a screwdriver
- ✓ Maximum contact and packing density in combination with double-level MCDN(V) 1,5 base strips
- ✓ Ultra-flat design height of just 7.8 mm
- ✓ Fast conductor connection thanks to Push-in spring-cage connection
- ✓ Wide range of possible combinations with all MC 1,5 base strips with 3.5 or 3.81 mm pitch
- ✓ Touch connection for voltage testing using a 1 mm Ø test pin

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 50            |
| GTIN             | 4017918942915 |

### Technical data

#### Dimensions

|             |         |
|-------------|---------|
| Length      | 22.9 mm |
| Height      | 7.8 mm  |
| Pitch       | 3.5 mm  |
| Dimension a | 24.5 mm |

#### General

|                                  |                     |
|----------------------------------|---------------------|
| Range of articles                | FMC 1,5/...-ST      |
| Insulating material group        | I                   |
| Rated surge voltage (III/3)      | 2.5 kV              |
| Rated surge voltage (III/2)      | 2.5 kV              |
| Rated surge voltage (II/2)       | 2.5 kV              |
| Rated voltage (III/3)            | 160 V               |
| Rated voltage (III/2)            | 160 V               |
| Rated voltage (II/2)             | 320 V               |
| Connection in acc. with standard | EN-VDE              |
| Nominal current I <sub>N</sub>   | 8 A                 |
| Nominal cross section            | 1.5 mm <sup>2</sup> |

# Printed-circuit board connector - FMC 1,5/ 8-ST-3,5 - 1952322

## Technical data

### General

|                                         |       |
|-----------------------------------------|-------|
| Maximum load current                    | 8 A   |
| Insulating material                     | PA    |
| Inflammability class according to UL 94 | V0    |
| Internal cylindrical gage               | A1    |
| Stripping length                        | 10 mm |
| Number of positions                     | 8     |

### Connection data

|                                                                            |                      |
|----------------------------------------------------------------------------|----------------------|
| Conductor cross section solid min.                                         | 0.2 mm <sup>2</sup>  |
| Conductor cross section solid max.                                         | 1.5 mm <sup>2</sup>  |
| Conductor cross section stranded min.                                      | 0.2 mm <sup>2</sup>  |
| Conductor cross section stranded max.                                      | 1.5 mm <sup>2</sup>  |
| Conductor cross section stranded, with ferrule without plastic sleeve min. | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule without plastic sleeve max. | 1.5 mm <sup>2</sup>  |
| Conductor cross section stranded, with ferrule with plastic sleeve min.    | 0.25 mm <sup>2</sup> |
| Conductor cross section stranded, with ferrule with plastic sleeve max.    | 0.75 mm <sup>2</sup> |
| Conductor cross section AWG/kcmil min.                                     | 24                   |
| Conductor cross section AWG/kcmil max                                      | 16                   |
| Minimum AWG according to UL/CUL                                            | 24                   |
| Maximum AWG according to UL/CUL                                            | 16                   |

## classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 272607xx |
| eCl@ss 4.1 | 27260701 |
| eCl@ss 5.0 | 27260701 |
| eCl@ss 5.1 | 27260701 |
| eCl@ss 6.0 | 27260704 |
| eCl@ss 7.0 | 27440402 |
| eCl@ss 8.0 | 27440402 |

### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC001121 |
| ETIM 4.0 | EC002638 |
| ETIM 5.0 | EC002638 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211810 |
| UNSPSC 7.0901 | 39121409 |
| UNSPSC 11     | 39121409 |

# Printed-circuit board connector - FMC 1,5/ 8-ST-3,5 - 1952322

## classifications

### UNSPSC

|                     |          |
|---------------------|----------|
| <b>UNSPSC 12.01</b> | 39121409 |
| <b>UNSPSC 13.2</b>  | 39121409 |

## approvals

UL Recognized / cUL Recognized / GOST / GOST / cULus Recognized /

### Approval details

| <b>UL Recognized</b>  |       |       |
|--------------------------------------------------------------------------------------------------------|-------|-------|
| Usegroups                                                                                              | B     | D     |
| Nominal voltage UN                                                                                     | 150 V | 150 V |
| Nominal current IN                                                                                     | 8 A   | 8 A   |
| mm²/AWG/kcmil                                                                                          | 24-16 | 24-16 |

| <b>cUL Recognized</b>  |       |       |
|-----------------------------------------------------------------------------------------------------------|-------|-------|
| Usegroups                                                                                                 | B     | D     |
| Nominal voltage UN                                                                                        | 150 V | 150 V |
| Nominal current IN                                                                                        | 8 A   | 8 A   |
| mm²/AWG/kcmil                                                                                             | 24-16 | 24-16 |

|                                                                                                 |
|-------------------------------------------------------------------------------------------------|
| <b>GOST</b>  |
|-------------------------------------------------------------------------------------------------|

|                                                                                     |
|-------------------------------------------------------------------------------------|
|  |
|-------------------------------------------------------------------------------------|

|                                                                                                             |
|-------------------------------------------------------------------------------------------------------------|
| <b>cULus Recognized</b>  |
|-------------------------------------------------------------------------------------------------------------|

## accessories

### Labeled terminal marker

## Printed-circuit board connector - FMC 1,5/ 8-ST-3,5 - 1952322

### accessories

SK 3,5/2,8:FORTL.ZAHLEN - 0804073



---

### Terminal marking

SK U/2,8 WH:UNBEDRUCKT - 0803883



---

### Marker pen

B-STIFT - 1051993



---

### accessories

SK 3,5/2,8:SO - 0805030




---


### Drawings

## Printed-circuit board connector - FMC 1,5/ 8-ST-3,5 - 1952322

Diagram




Diagram



Type: FMC 1,5/...-ST-3,5 with MCV 1,5/...-G-3,5 P26 THR

## Printed-circuit board connector - FMC 1,5/ 8-ST-3,5 - 1952322

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>