

Feed-through terminal block - ST 1,5-QUATTRO-PE - 3031209

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Spring-cage connection, Cross section: 0.08 mm² - 1.5 mm², AWG: 28 - 16, Width: 4.2 mm, Color: green-yellow, Mounting type: NS 35/7,5, NS 35/15

Product Features

- ☒ Additional labeling options
- ☒ Tested for railway applications
- ☒ Low contact resistance
- ☒ Corrosion-free terminal points
- ☒ Green-yellow housing



Key commercial data

package_quantity	50
GTIN	4017918186692

Technical data

General

Number of levels	1
Number of connections	2
Color	green-yellow
Insulating material	PA
Inflammability class according to UL 94	V0
Area of application	Railway industry
Area of application	Mechanical engineering
Area of application	Plant engineering
Area of application	Process industry

General

Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-2

Feed-through terminal block - ST 1,5-QUATTRO-PE - 3031209

Technical data

General

Open side panel	ja
-----------------	----

Dimensions

Width	4.2 mm
Length	72 mm
Height NS 35/7,5	36.5 mm
Height NS 35/15	44 mm

Connection data

Conductor cross section solid min.	0.08 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	28
Conductor cross section AWG/kcmil max	16
Conductor cross section stranded min.	0.08 mm ²
Conductor cross section stranded max.	1.5 mm ²
Min. AWG conductor cross section, stranded	28
Max. AWG conductor cross section, stranded	16
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	1.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	1.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	0.5 mm ²
Connection method	Spring-cage connection
Stripping length	10 mm
Internal cylindrical gage	A 1

classifications

eCl@ss

eCl@ss 4.0	27141121
eCl@ss 4.1	27141121
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000901
ETIM 3.0	EC000901

Feed-through terminal block - ST 1,5-QUATTRO-PE - 3031209

classifications

ETIM

ETIM 4.0	EC000901
ETIM 5.0	EC000901

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

IECEX / ATEX / CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / GOST / LR / GL / BV / DNV / RS / KR / NK / IECCE CB Scheme / GOST / cULus Recognized /

Approval details

IECEX	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	0.08-1.5

ATEX 	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	0.08-1.5

CSA 	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	26-14

UL Recognized 	
--	--

Feed-through terminal block - ST 1,5-QUATTRO-PE - 3031209

approvals

Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	26-14

VDE Gutachten mit Fertigungsüberwachung 	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	0.2-1.5

cUL Recognized 	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	26-14

GOST 	
---	--

LR

GL	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	1.5

BV

DNV

RS


KR

NK

Feed-through terminal block - ST 1,5-QUATTRO-PE - 3031209

approvals

IECEE CB Scheme 	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	0.2-1.5



accessories

End cover

D-ST 2,5-QUATTRO - 3030514



DS-ST 2,5 - 3036602



D-ST 2,5-QUATTRO-0,8 OG - 3030513



Partition plate

Feed-through terminal block - ST 1,5-QUATTRO-PE - 3031209

accessories

ATP-ST QUATTRO - 3030815



Screwdriver tools

SZF 0-0,4X2,5 - 1204504



Documentation

ST-IL - 3039900



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



Feed-through terminal block - ST 1,5-QUATTRO-PE - 3031209

accessories

NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



Feed-through terminal block - ST 1,5-QUATTRO-PE - 3031209

accessories

NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



Feed-through terminal block - ST 1,5-QUATTRO-PE - 3031209

accessories

NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Feed-through terminal block - ST 1,5-QUATTRO-PE - 3031209

accessories

Terminal marking

ZB 4 :UNBEDRUCKT - 0805001



UC-TM 4 - 0818111



UCT-TM 4 - 0828732



ZBF 4:UNBEDRUCKT - 0808587



UC-TMF 4 - 0818166



Feed-through terminal block - ST 1,5-QUATTRO-PE - 3031209

accessories

UCT-TMF 4 - 0828742



Labeled terminal marker

ZB 4 CUS - 0824951



UC-TM 4 CUS - 0824573



UCT-TM 4 CUS - 0829588



ZBF 4 CUS - 0825023



Feed-through terminal block - ST 1,5-QUATTRO-PE - 3031209

accessories

UC-TMF 4 CUS - 0824630



UCT-TMF 4 CUS - 0829651



Insulating sleeve

ISH 1,5/0,2 - 3206131



ISH 1,5/0,5 - 3031034



End block

CLIPFIX 35 - 3022218



Feed-through terminal block - ST 1,5-QUATTRO-PE - 3031209

accessories

CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



E/UK - 1201442




E/UK 1 - 1201413



Drawings

Feed-through terminal block - ST 1,5-QUATTRO-PE - 3031209

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>