

# Mounting flange - HC-B-AF-SET - 1604638

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Panel mounting flange for screw locking, set comprising 2 panel mounting flanges with 4 self-tapping Torx® head screws and 4 fan-type washers

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4017918893262

## Technical data

### Ambient conditions

<b>Ambient temperature (operation)</b>	-40 °C ... 125 °C
--	-------------------

### General

<b>Material</b>	Zinc die-cast
<b>Note</b>	1 for every connector
<b>Assembly instructions</b>	In order to guarantee that the ground conductor contact functions even when plugged in at an angle, the two panel mounting flanges must have sufficient electrical contact with the metal mounting panel.
<b>Connection</b>	Minimum panel thickness of a steel sheet: 2.0 mm

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	272607xx
<b>eCl@ss 4.1</b>	27140816
<b>eCl@ss 5.0</b>	27371205
<b>eCl@ss 5.1</b>	27371205
<b>eCl@ss 6.0</b>	27371205
<b>eCl@ss 7.0</b>	27371205
<b>eCl@ss 8.0</b>	27371205

### ETIM

<b>ETIM 2.0</b>	EC000437
<b>ETIM 3.0</b>	EC000437
<b>ETIM 4.0</b>	EC000437
<b>ETIM 5.0</b>	EC002310

# Mounting flange - HC-B-AF-SET - 1604638

classifications


UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

approvals

GOST /

Approval details



Drawings

Dimensioned drawing

