

## Insert label - EMT (50X26)R TQ - 0800053

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Insert label, Roll, turquoise, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Snapped into marker carrier, Lettering field: 50 x 26 mm

The figure shows the white version

### Product Features

- Can be printed using all the thermal transfer printers available from Phoenix Contact
- Insertable conductor marking for marking collars
- Thanks to their special shape, insert labels remain securely inside the collar once inserted
- Insert labels for marking various marking collars
- Available in three colors
- Precise printing quality
- EMT ... insert strips are available in various sizes for marking controllers and modules from other manufacturers

### Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4046356545570

### Technical data

#### Dimensions

<b>Length (b)</b>	50 mm
<b>Width (a)</b>	26 mm

#### Ambient conditions

<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
<b>Ambient temperature (operation)</b>	-40 °C ... 120 °C
<b>Recommended storage conditions</b>	23 °C / 50 % relative humidity

#### General

<b>Color</b>	turquoise
<b>Components</b>	free from silicone and halogen
<b>Material</b>	Polyester
<b>Number of individual labels</b>	500
<b>Number of individual labels per row</b>	2
<b>RoHS compliant</b>	Yes
<b>Printability</b>	Thermal transfer

## Insert label - EMT (50X26)R TQ - 0800053

### Technical data

#### General

Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	KFW 1.0 S
Cycles	2
Condensation test result	Test passed
Foil strength	175 µm

### classifications

#### eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

#### ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC001694
ETIM 5.0	EC001675

#### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

### accessories

#### Ink ribbon

## Insert label - EMT (50X26)R TQ - 0800053

accessories

THERMOMARK-RIBBON 110 - 5145384



---

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>