

Feed-through terminal block - PTS 1,5/S BU - 3214550

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Push-in connection, Cross section: 0.14 mm² - 1.5 mm², AWG: 26 - 14, Width: 3.5 mm, Height: 37 mm, Color: blue, Mounting type: NS 35/7,5, NS 35/15

Key commercial data

package_quantity	50
GTIN	4046356616294

Technical data

General

Number of levels	1
Number of connections	2
Color	blue
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	17.5 A (with 1.5 mm ² conductor cross section)
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	17.5 A
Nominal voltage U _N	500 V
Open side panel	ja

Dimensions

Width	3.5 mm
Length	50.7 mm
Height	37 mm
Height NS 35/7,5	38.5 mm
Height NS 35/15	46 mm

Connection data

Conductor cross section solid min.	0.14 mm ²
------------------------------------	----------------------

Feed-through terminal block - PTS 1,5/S BU - 3214550

Technical data

Connection data

Conductor cross section solid max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
Conductor cross section stranded min.	0.14 mm ²
Conductor cross section stranded max.	1.5 mm ²
Min. AWG conductor cross section, stranded	26
Max. AWG conductor cross section, stranded	14
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	1.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.14 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	1 mm ²
Connection method	Push-in connection
Stripping length	8 mm
Internal cylindrical gage	A1 / B1

classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

Feed-through terminal block - PTS 1,5/S BU - 3214550

approvals

Approval details

UL Recognized 			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	15 A	15 A	5 A
mm²/AWG/kcmil	26-14	26-14	26-14

cUL Recognized 			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	15 A	15 A	5 A
mm²/AWG/kcmil	26-14	26-14	26-14

LR

CSA 			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	15 A	15 A	5 A
mm²/AWG/kcmil	26-14	26-14	26-14

GOST 			
--	--	--	--

GL

cULus Recognized 			
--	--	--	--

accessories

Marker carriers

Feed-through terminal block - PTS 1,5/S BU - 3214550

accessories

GBS-ZB/26X6 - 0809298



Screwdriver tools

SZF 0-0,4X2,5 - 1204504



Partition plate

ATP-ST 4 - 3030721



End cover

D-PTS 1,5/S - 3214576



Documentation

PT-IL - 3208090



Feed-through terminal block - PTS 1,5/S BU - 3214550

accessories

Bridge

FBS 3-3,5 BU - 3213099



FBS 4-3,5 BU - 3213109



FBS 5-3,5 BU - 3213112



FBS 10-3,5 BU - 3213125



FBS 20-3,5 BU - 3213138



Feed-through terminal block - PTS 1,5/S BU - 3214550

accessories

RB ST (2,5/4)-1,5/S - 3214356



RB ST 6-1,5/S - 3213250



FBS 2-3,5 - 3213014



FBS 3-3,5 - 3213027



FBS 4-3,5 - 3213030



FBS 5-3,5 - 3213043



Feed-through terminal block - PTS 1,5/S BU - 3214550

accessories

FBS 10-3,5 - 3213056



FBS 20-3,5 - 3213069



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



Feed-through terminal block - PTS 1,5/S BU - 3214550

accessories

NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



Feed-through terminal block - PTS 1,5/S BU - 3214550

accessories

NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



Feed-through terminal block - PTS 1,5/S BU - 3214550

accessories

NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

Feed-through terminal block - PTS 1,5/S BU - 3214550

accessories

ZB 3,5:UNBEDRUCKT - 0829414



UCT-TM 3,5 - 0829484



ZBF 3,5:UNBEDRUCKT - 0829392



UCT-TMF 3,5 - 0829486



TMT (EX9,5)R - 0828295



Labeled terminal marker

Feed-through terminal block - PTS 1,5/S BU - 3214550

accessories

ZB 3,5 CUS - 0829415



UCT-TM 3,5 CUS - 0829581



ZBF 3,5 CUS - 0829394



UCT-TMF 3,5 CUS - 0829644



Test plug terminal block

MPS-MT - 0201744



Insulating sleeve

Feed-through terminal block - PTS 1,5/S BU - 3214550

accessories

MPS-IH WH - 0201663



MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



Feed-through terminal block - PTS 1,5/S BU - 3214550

accessories

MPS-IH BK - 0201731



Planning and marking software

CLIP-PROJECT ADVANCED - 5146040



CLIP-PROJECT PROFESSIONAL - 5146053



End block

E/UK - 1201442



E/UK 1 - 1201413



Feed-through terminal block - PTS 1,5/S BU - 3214550

accessories

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



Drawings

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>