

Sleeve frame - VC-TR2/3M - 1852901

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Sleeve frame, without PE, for contact insert modules, type 2, number of insert modules 3

The illustration shows the version VC-TR 1/2 M

Key commercial data

package_quantity	5
GTIN	4017918133740

Technical data

Dimensions

Height	27.5 mm
Width	65.2 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

General

Design	VC2
Color	black
Material	PA-GF
Housing material	Plastic
Inflammability class according to UL 94	V0

classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27189239
eCl@ss 5.1	27189239
eCl@ss 6.0	27144001
eCl@ss 7.0	27144001
eCl@ss 8.0	27144001

ETIM

Sleeve frame - VC-TR2/3M - 1852901

classifications

ETIM

ETIM 2.0	EC000007
ETIM 3.0	EC000007
ETIM 4.0	EC000007
ETIM 5.0	EC000007



UNSPSC

UNSPSC 6.01	43172601
UNSPSC 7.0901	31261501
UNSPSC 11	43172601
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

approvals

UL Recognized / cUL Recognized / cULus Recognized /


Approval details



Drawings

Sleeve frame - VC-TR2/3M - 1852901

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>