

# Marker for terminal blocks - UCT-TM 7,62 - 0828738

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Marker for terminal blocks, Sheet, white, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, BLUEMARK CLED, BLUEMARK LED, Mounting type: Snap into tall marker groove, For terminal block width: 7.62 mm, Lettering field: 7 x 10.5 mm

## Product Features

- Labeling service: Phoenix Contact can custom-label all UniCard markers according to your requirements
- The UCT-TM... UniCard labeling range includes markers for products with tall marker grooves

## Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4046356523479

## Technical data

### Dimensions

<b>Length (b)</b>	10.5 mm
<b>Height</b>	4.76 mm
<b>Width (a)</b>	7 mm

### Ambient conditions

<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
<b>Ambient temperature (operation)</b>	-40 °C ... 120 °C

### General

<b>Note</b>	Can be labeled via thermal transfer
<b>Color</b>	white
<b>Components</b>	free from silicone and halogen
<b>Inflammability class according to UL 94</b>	V0
<b>Material</b>	PC
<b>Material</b>	PC
<b>Number of individual labels</b>	48
<b>Number of individual labels per row</b>	8
<b>RoHS compliant</b>	Yes
<b>Printability</b>	Thermal transfer
<b>Printability</b>	Inkjet printing
<b>Test for substances that would hinder coating with paint or varnish</b>	VW PV 3.10.7:2005-02
<b>Result</b>	Test passed

## Marker for terminal blocks - UCT-TM 7,62 - 0828738

### Technical data

#### General

<b>Test specification weathering-resistance</b>	Following ISO 4892-2:2013-03
<b>Test duration</b>	96 h
<b>Wipe resistance test result</b>	Test passed
<b>Salt spray test specification</b>	DIN EN ISO 9227:2012-09
<b>Test duration</b>	96 h
<b>Salt spray testing result</b>	Test passed
<b>Alternating condensation climate with SO2 test specification</b>	DIN 50018:1997-06
<b>Climate level</b>	KFW 1.0 S
<b>Cycles</b>	2
<b>Condensation test result</b>	Test passed
<b>Wipe resistance of test specification inscriptions</b>	IEC 61010-1:2010-06
<b>Result</b>	Test passed
<b>Burning behaviour</b>	V0

### classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	24190208
<b>eCl@ss 4.1</b>	24190208
<b>eCl@ss 5.0</b>	27149103
<b>eCl@ss 5.1</b>	27141137
<b>eCl@ss 6.0</b>	27141137
<b>eCl@ss 7.0</b>	27141137
<b>eCl@ss 8.0</b>	27141137

#### ETIM

<b>ETIM 2.0</b>	EC000761
<b>ETIM 3.0</b>	EC000761
<b>ETIM 4.0</b>	EC000761
<b>ETIM 5.0</b>	EC000761

#### UNSPSC

<b>UNSPSC 6.01</b>	30211811
<b>UNSPSC 7.0901</b>	39121410
<b>UNSPSC 11</b>	39121410
<b>UNSPSC 12.01</b>	39121410
<b>UNSPSC 13.2</b>	39121410

### accessories

#### Magazine

## Marker for terminal blocks - UCT-TM 7,62 - 0828738

accessories

THERMOMARK CARD-UCT-MAG1 - 5146480



---

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>