


DATA SHEET FOR B-405 INDICATOR LIGHT 24V RED



Parts List

Name	Materials	Finish or Colour
1) Body	Polycarbonate	Red (UL Flame Class V-2)
2) Spring / Washer	SWP	Ni-3
3) Hex Nut	BSBM2	Ni-3
4) Lamp		24V
5) Insulation Tube	IRRAX Tube	Black
6) Insulation Mould	NORIL	Black
7) Terminal	BSP	Ni-3

Specifications

Voltage Breakdown	: AC 1000V / minute
Insulation Resistance	: DC 500V 100M Ω or more
Voltage	: 24V
Operating Temperature	: -20°C ~ +75°C
Shape of Terminal	: Solder Terminal
Thread	: 7.00mm dia. X 10.0mm Length Pitch = 0.75mm
Mounting Hole	: 7.2mm dia. (Recommended)

Note about IP Code :

As the whole Body is made in single mould, neither dust nor water come into the Body from the Head. On the other hand, there are 2 gaps on the Bottom for inserting Terminals, but the part of Bottom will be covered by the enclosure of the finished product.