

# Cable marker - US-WMTB (29X8) YE - 0828959

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable marker, Card, yellow, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, Mounting type: Thread on, Cable diameter: >13 mm, Lettering field: 29 x 8 mm

The figure shows the US-WMTB (24x5) version

## Product Features

- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The US-WMTB... UniSheet labeling range includes markers that can be secured using standard cable binders
- The perforated marking strips are easy to separate and can be easily fitted
- The sheets provide space for including function texts

## Key commercial data

<b>package_quantity</b>	10
<b>GTIN</b>	4046356559904

## Technical data

### Dimensions

<b>Length (b)</b>	29 mm
<b>Width (a)</b>	16 mm

### Ambient conditions

<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
<b>Ambient temperature (operation)</b>	-30 °C ... 80 °C
<b>Recommended storage conditions</b>	10-30 °C / 40-70 % relative humidity. Storage in poly bags is recommended prior to processing.

### General

<b>Color</b>	yellow
<b>Components</b>	Silicone-free
<b>Inflammability class according to UL 94</b>	V0
<b>Material</b>	PVC
<b>Number of individual labels</b>	24
<b>Number of individual labels per row</b>	6
<b>Printability</b>	Thermal transfer
<b>Test for substances that would hinder coating with paint or varnish</b>	VW PV 3.10.7:2005-02

# Cable marker - US-WMTB (29X8) YE - 0828959

## Technical data

### General

<b>Result</b>	Test passed
<b>Test specification weathering-resistance</b>	Following ISO 4892-2:2013-03
<b>Test duration</b>	96 h
<b>Wipe resistance test result</b>	Test passed
<b>Salt spray test specification</b>	DIN EN 60068-2-11:2000-02
<b>Test duration</b>	96 h
<b>Salt spray testing result</b>	Test passed
<b>Alternating condensation climate with SO2 test specification</b>	Following DIN 50018:2013-05
<b>Climate level</b>	AHT 1.0 S
<b>Cycles</b>	2
<b>Condensation test result</b>	Test passed
<b>Wipe resistance of test specification inscriptions</b>	DIN EN 61010-1 (VDE 0411-1):2011-07
<b>Result</b>	Test passed

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	24190218
<b>eCl@ss 4.1</b>	24190218
<b>eCl@ss 5.0</b>	27141137
<b>eCl@ss 5.1</b>	27141137
<b>eCl@ss 6.0</b>	27400401
<b>eCl@ss 7.0</b>	27400401
<b>eCl@ss 8.0</b>	27400401

### ETIM

<b>ETIM 2.0</b>	EC000761
<b>ETIM 3.0</b>	EC000761
<b>ETIM 4.0</b>	EC001530
<b>ETIM 5.0</b>	EC001530

### UNSPSC

<b>UNSPSC 6.01</b>	30211811
<b>UNSPSC 7.0901</b>	39121410
<b>UNSPSC 11</b>	39121410
<b>UNSPSC 12.01</b>	39121410
<b>UNSPSC 13.2</b>	39121410

## accessories

### Magazine

## Cable marker - US-WMTB (29X8) YE - 0828959

accessories

THERMOMARK CARD-US-MAG1 - 5146451



---

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>