





**2-CONDUCTOR SPRING CLAMPS  
WITH LOCKING LEVER PIN SPACING  
5.08 MM / 0.2 IN  
231-2302/037-000 TO 231-2316/037-000**

<b>ITEM-NO. (ITEM-NO.)</b>	231-2304/037-000
<b>Cross section1 (Cross section / mm<sup>2</sup>)</b>	0.2 - 2.5
<b>Cross section2 (Cross section / AWG)</b>	24 - 12
<b>Strip length (Strip length / mm)</b>	9 - 10
<b>Measured voltage (Measured voltage / V)</b>	320
<b>Measured shock voltage (Measured shock voltage / kV)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity / A)</b>	16
<b>RM (PIN SPACING / mm)</b>	5.08
<b>P (NO. OF POLES)</b>	4
<b>Height (Height / mm)</b>	20.8
<b>Width (Width / mm)</b>	36.71
<b>Depth (Depth / mm)</b>	29.8
<b>No. of connection Points (No. of connection Points)</b>	8
<b>No. of potentials (No. of potentials)</b>	4
<b>COLOR (COLOR)</b>	orange
<b>WEIGHT (WEIGHT / g)</b>	10.772
<b>Comment (Comment)</b>	$L = (\text{No. of poles} - 2) \times \text{Pin Spacing} + 10 \text{ mm}$