

Ad16 Series Pilot Lamp

Product Overview

Ad16 series pilot lamp only use LED lamp as the light source. The advantage have: long life, gentle weight, small cubage, save energy. It is the advanced product of all kinds of the incandescence lamp and the neon lamp of the XD type. The cover of the lamp is made of PC material, and have good shock resistance. It can be used as indication pilot light, accident signal and other signals in the circuits of such equipment as telecommunication.

Specifications

- Electrical Life ≥ 30000 hours
- Brightness: $\geq 100\text{cd/m}^2$
- Permitted Voltage $\pm 20\%$ ($\geq 110\text{V}$)
- Comparative Tracking Index CT1 ≥ 100 , flame retardant
- Dielectric Strength: 2.5kV(AC RMS) , 1min
- Insulation Resistance: $U_i \leq 60\text{V}$, $5\text{M}\Omega$; $60\text{V} < U_i \leq 660\text{V}$, $50\text{M}\Omega$
- Usage Frequency (AC): $50 \sim 60\text{Hz}$
- Light Color: red, green, yellow, white, blue, orange
- Rated Operating Current: $\leq 20\text{mA}$
- Operating Temperature: $-25^\circ\text{C} \sim 55^\circ\text{C}$

Implication of Type

AD16	-	★	■	□	/	△	/	▲	/	●	/
Code of series	The installation dimension of the neck; 16: $\Phi 16\text{mm}$ 22: $\Phi 22\text{mm}$	The design code (A,B,C..... express different type of the same neck dimension) M buzzer S flicker SM flicker buzzer SS Dual - color lamp	S expresses the super short type, the standard type is without letter.	Color of pilot lamp: R red G green Y yellow O orange W white B blue	Voltage	K expresses anti-interference type, the normal type is without letter.					

Diagram of Interior Connection

	AC/DC Type Pilot Lamp	AC Type Pilot Lamp	AC/DC Type Dual-color Lamp	AC Type Dual-color Lamp
Normal Type				
Anti-interference Type				





Note: 1, AC/DC type pilot lamp is resistor step - down form; AC type pilot lamp is capacitor step - down form.

2, When voltage is 110V or above it, The temperature of outer shell of AC/DC type pilot lamp is higher than AC type pilot lamp.

Attentions







- The frequency of AC type pilot lamp is $50 \sim 60\text{Hz}$. If work in other frequency ranges, it will be broken.
- The common threshold value of anti-interference pilot lamp is below 40V ; and if you need higher threshold value please tell us. We suggest that the threshold value should n't be too high. Please check the routing if the interference voltage is too high.
- Connection error is not allowable to AC type dual-color light, otherwise pilot lamp will be broken.
- Avoid using welding mode to connect lines as possible and you should using general plug ($2.5 \times 0.8\text{mm}$) to connect and wear the protective sleeve. If you need to weld, please finish it in 3 seconds by the electric iron which is below 30W and don't exert external force on terminals.





Product Outline(Φ16)

Shape	Type Number	Color	Operating Voltage	Shape & Dimensions	Remarks
Φ16A 	AD16 - 16A/△/▲	R G Y B W	AC/DC 6V AC/DC 12V AC/DC 24V AC/DC 36V AC/DC 48V		Pin terminal
Φ16B 	AD16 - 16B/△/▲	R G Y B W	AC/DC 110V AC/DC 230V AC/DC 380V AC 110V AC 230V AC 380V		Pin terminal
Φ16E 	AD16 - 16E/△/▲	R G Y O B W	AC/DC 6V AC/DC 12V AC/DC 24V AC/DC 36V AC/DC 48V AC/DC 110V AC/DC 230V AC/DC 380V AC 110V AC 230V AC 380V		⦿ Screw terminal ⦿ Electric Shock Protection Structure
Φ16 Flicker Buzzer 	AD16 - 16M/▲	Buzzer	AC/DC 110V AC/DC 230V AC/DC 380V AC 110V AC 230V AC 380V		Sound Intensity: Volume ≥80dB(10cm) Continuous Buzz Incontinuous Buzz Ie≤28mA Frequency 2300±300Hz
	AD16 - 16S/▲	Flicker Lamp			
	AD16 - 16SM/▲	Flicker Buzzer			

Ad16 Series Pilot Lamp

Product Outline(Φ22)

Shape	Type Number	Color	Operating Voltage	Shape & Dimensions	Remarks
Φ22BS (super short type) 	AD16 - 22BS/△/▲	R G Y O B W	AC/DC 6V AC/DC 12V AC/DC 24V AC/DC 36V AC/DC 48V AC/DC 110V AC/DC 230V AC/DC 380V AC 110V AC 230V AC 380V		⊙ Screw Type Connection ⊙ Electric Shock Protection Structure
Φ22DS(super short type) 	AD16 - 22DS/△/▲/⊙	R G Y O B W			⊙ Screw Type Connection ⊙ Electric Shock Protection Structure
Φ22ES(super short type) 	AD16 - 22ES/△/▲	R G Y O B W			⊙ Screw Type Connection ⊙ Electric Shock Protection Structure
Φ22HS(super short type) 	AD16 - 22HS/△/▲	R G Y O B W			⊙ Screw Type Connection ⊙ Electric Shock Protection Structure
Φ22B 	AD16 - 22B/△/▲/●	R G Y O B W			⊙ Screw Type Connection ⊙ Electric Shock Protection Structure ⊙ Anti-interference type can be customized.
Φ22D 	AD16 - 22D/△/▲/●/⊙	R G Y O B W			⊙ Screw Type Connection ⊙ Electric Shock Protection Structure ⊙ Anti-interference type can be customized.

Shape	Type Number	Color	Operating Voltage	Shape & Dimensions	Remarks
Φ22E 	AD16 - 22E /△/▲/●	R G Y O B W	AC/DC 6V AC/DC 12V AC/DC 24V AC/DC 36V AC/DC 48V AC/DC 110V AC/DC 230V AC/DC 380V AC 110V AC 230V AC 380V		⊙ Screw Type Connection ⊙ Electric Shock Protection Structure ⊙ Anti-interference type can be customized.
Φ22H 	AD16 - 22H /△/▲/●	R G Y O B W			⊙ Screw Type Connection ⊙ Electric Shock Protection Structure ⊙ Anti-interference type can be customized.
Φ22 Two - color Pilot Lamp 	AD16 - 22SS /△/▲/●	R G			⊙ Screw Type Connection ⊙ Electric Shock Protection Structure ⊙ Anti-interference type can be customized. ⊙ Other color types can be customized.
Φ22 Flicker Buzzer 	AD16 - 22M/▲ AD16 - 22S/▲ AD16 - 22SM/▲	Buzzer Flicker Lamp Flicker Buzzer			Sound Intensity: Volume ≥80 dB(10cm) Continuous Buzz Incontinuous Buzz Ie≤28mA Frequency 2300±300Hz