



**HEADER (FOR PRINTED CIRCUIT  
BOARDS) RIGHT ANGLE SOLDER  
PIN, 1 X 1 MM / 0.039 X 0.039 IN PIN  
SPACING 5,08 mm / 0.2 in  
231-532/108/000 TO 231-546/108-000**

|   |  |
|---|--|
| <b>ITEM-NO. (ITEM-NO.)</b>                                  | 231-546/108-000  |
| <b>Measured voltage (Measured voltage / V)</b>              | 320  |
| <b>Measured shock voltage (Measured shock voltage / kV)</b> | 4  |
| <b>Pollution degree (Pollution degree)</b>                  | 2  |
| <b>Current intensity (Current intensity / A)</b>            | 12   |
| <b>RM (PIN SPACING / mm)</b>                                | 5.08   |
| <b>P (NO. OF POLES)</b>                                     | 16   |
| <b>Height (Height / mm)</b>                                 | 8.4  |
| <b>Width (Width / mm)</b>                                   | 91.18  |
| <b>Depth (Depth / mm)</b>                                   | 12   |
| <b>COLOR (COLOR)</b>  | orange   |
| <b>WEIGHT (WEIGHT / g)</b>                                  |  |
| <b>Comment (Comment)</b>                                    | L1 = (No. of poles x Pin Spacing) + 5,9 mm  <br>L2 = (No. of poles x Pin Spacing) + 9,9 mm |
| <b>Dimensions (Dimensions)</b>                              | 1,4 + 0,1 mm   |