

Connector - BNC-DV 75 - 2805083

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



BNC connector, double-level, for mounting on NS 32 or NS 35/7.5, wave impedance: 75 Ohm

Product Features

- Can be labeled individually
- With isolated structure on the DIN rail
- DIN rail-mountable and can be aligned
- For coaxial cables

Key commercial data

package_quantity	10
GTIN	4017918074579

Technical data

Dimensions

Height	90 mm
Width	22 mm
Length	42.5 mm

Ambient conditions

Ambient temperature (operation)	125 °C
Degree of protection	IP20

General

Housing material	PA
Inflammability class according to UL 94	V2
Color	gray
Mounting type	NS 35/7,5

Protective circuit

Frequency range	0 GHz ... 3 GHz
Standing wave ratio SWR in a 75 Ω system	< 1.1 (3 GHz)

Connection data

Connection method	BNC 75 Ω
--------------------------	----------

Connector - BNC-DV 75 - 2805083

classifications

eCl@ss

eCl@ss 4.0	27141131
eCl@ss 4.1	27141131
eCl@ss 5.0	27141131
eCl@ss 5.1	27141131
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002498
ETIM 5.0	EC002498

UNSPSC

UNSPSC 6.01	30211802
UNSPSC 7.0901	39121402
UNSPSC 11	39121410
UNSPSC 12.01	39121404
UNSPSC 13.2	39121404

approvals

GOST /

Approval details



accessories

Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



Connector - BNC-DV 75 - 2805083

accessories

NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



Connector - BNC-DV 75 - 2805083

accessories

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>