

Installation terminal block - UTI 16 BU - 3075728

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Installation terminal block, Special and hybrid connection, Cross section: 6 mm² - 25 mm², AWG: 10 - 4, Width: 12.2 mm, Color: blue, Mounting type: NS 35/7,5, NS 35/15

Product Features

- ✓ The installation terminal block features a particularly low-profile design and is suitable for wiring in flat installation distributors
- ✓ The asymmetrical arrangement of the terminal blocks on the DIN rail enables the neutral busbar to be routed past the terminal blocks

Key commercial data

package_quantity	50
GTIN	4046356518031

Technical data

General

Number of levels	1
Number of connections	2
Color	blue
Insulating material	PA
Inflammability class according to UL 94	V2

General

Maximum load current	76 A (with 16 mm ² conductor cross section)
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	76 A
Nominal voltage U _N	400 V
Open side panel	nein

Dimensions

Width	12.2 mm
Length	51 mm
Height	49.90 mm
Height NS 35/7,5	50.5 mm

Installation terminal block - UTI 16 BU - 3075728

Technical data

Dimensions

Height NS 35/15	58 mm
-----------------	-------

Connection data

Note	Terminal point
Conductor cross section solid min.	6 mm ²
Conductor cross section solid max.	25 mm ²
Conductor cross section AWG/kcmil min.	10
Conductor cross section AWG/kcmil max	4
Conductor cross section stranded min.	6 mm ²
Conductor cross section stranded max.	16 mm ²
Min. AWG conductor cross section, stranded	10
Max. AWG conductor cross section, stranded	3
Conductor cross section stranded, with ferrule without plastic sleeve min.	6 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	16 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	6 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	16 mm ²
2 conductors with same cross section, solid min.	2.5 mm ²
2 conductors with same cross section, solid max.	10 mm ²
2 conductors with same cross section, stranded min.	2.5 mm ²
2 conductors with same cross section, stranded max.	6 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	4 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	6 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	4 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	6 mm ²
Connection method	Special and hybrid connection
Stripping length	12 mm
Screw thread	M5
Tightening torque, min	2.5 Nm
Tightening torque max	3 Nm

classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120

Installation terminal block - UTI 16 BU - 3075728

classifications

eCl@ss

eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897


UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

GOST /

Approval details



accessories

Pick-off terminal block

EK 116 - 0401010



EK 135 - 0401023



Installation terminal block - UTI 16 BU - 3075728

accessories

Support

UAB - 3032428



AB/NS - 1201141



Terminal marking

SBS10:UNBEDRUCKT - 1007248



ZB 12:UNPRINTED - 0812120



UC-TM 12 - 0819194



Installation terminal block - UTI 16 BU - 3075728

accessories

UCT-TM 12 - 0829144



Screwdriver tools

SZS 1,0X6,5 VDE - 1205079



Warning label printed

WS 4-12 - 0805328



WS 5-12 - 0805315



Bridge

FBI 2-12 - 0200075



Installation terminal block - UTI 16 BU - 3075728

accessories

FBI 10-12 - 0203454



EB 10-12 - 3006137



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



Installation terminal block - UTI 16 BU - 3075728

accessories

NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



Installation terminal block - UTI 16 BU - 3075728

accessories

NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



Installation terminal block - UTI 16 BU - 3075728

accessories

NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Labeled terminal marker

Installation terminal block - UTI 16 BU - 3075728

accessories

ZB 12 CUS - 0824942



UC-TM 12 CUS - 0824613



UCT-TM 12 CUS - 0829630



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



Installation terminal block - UTI 16 BU - 3075728

accessories

E/NS 35 N - 0800886



E/UK - 1201442



E/UK 1 - 1201413



Drawings

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>