



ITEM-NO. (ITEM-NO.)	231-632
Cross section1 (Cross section / mm²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 12
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	12
RM (PIN SPACING / mm)	5.08
P (NO. OF POLES)	2
Height (Height / mm)	14.3
Width (Width / mm)	13.36
Depth (Depth / mm)	27.5
No. of connection Points (No. of connection Points)	2
No. of potentials (No. of potentials)	2
COLOR (COLOR)	orange
WEIGHT (WEIGHT / g)	3.47
Comment (Comment)	A = (No. of poles x Pin Spacing) + 3,2 mm B = A - 1,7 mm C = A - 1,2 mm