

# Insert label - EMT (10X4)R - 0816235

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Insert label, Roll, white, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Insert, Cable diameter: 0.6-7 mm, Lettering field: 10 x 4 mm

The figure shows the EMT (40x17)R version

## Product Features

- PABL ... sheets are available for labeling with a laser printer
- Can be printed with THERMOMARK... for material off the roll
- Thanks to their special shape, EMT ... insert labels remain securely inside the collar once inserted
- EMT ... insert labels for labeling various marking collars

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4046356123396

## Technical data

### Dimensions

<b>Length (b)</b>	10 mm
<b>Width (a)</b>	4 mm

### Ambient conditions

<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
<b>Ambient temperature (operation)</b>	-40 °C ... 120 °C
<b>Recommended storage conditions</b>	23 °C / 50 % relative humidity

### General

<b>Color</b>	white
<b>Components</b>	free from silicone and halogen
<b>Material</b>	Polyester
<b>Number of individual labels</b>	7500
<b>Number of individual labels per row</b>	10
<b>Printability</b>	Thermal transfer
<b>Test for substances that would hinder coating with paint or varnish</b>	VW PV 3.10.7:2005-02
<b>Result</b>	Test passed
<b>Test specification weathering-resistance</b>	Following ISO 4892-2:2013-03
<b>Test duration</b>	96 h

## Insert label - EMT (10X4)R - 0816235

### Technical data

#### General

<b>Wipe resistance test result</b>	Test passed
<b>Salt spray test specification</b>	DIN EN 60068-2-11:2000-02
<b>Test duration</b>	96 h
<b>Salt spray testing result</b>	Test passed
<b>Alternating condensation climate with SO2 test specification</b>	Following DIN 50018:2013-05
<b>Climate level</b>	AHT 1.0 S
<b>Cycles</b>	2
<b>Condensation test result</b>	Test passed
<b>Wipe resistance of test specification inscriptions</b>	DIN EN 61010-1 (VDE 0411-1):2011-07
<b>Result</b>	Test passed
<b>Foil strength</b>	175 µm

### classifications

#### eCl@ss

<b>eCl@ss 4.0</b>	24190219
<b>eCl@ss 4.1</b>	24190219
<b>eCl@ss 5.0</b>	27149103
<b>eCl@ss 5.1</b>	27400401
<b>eCl@ss 6.0</b>	27400401
<b>eCl@ss 7.0</b>	27400401
<b>eCl@ss 8.0</b>	27400401

#### ETIM

<b>ETIM 2.0</b>	EC000761
<b>ETIM 3.0</b>	EC000761
<b>ETIM 4.0</b>	EC001530
<b>ETIM 5.0</b>	EC001530

#### UNSPSC

<b>UNSPSC 6.01</b>	30211811
<b>UNSPSC 7.0901</b>	39121410
<b>UNSPSC 11</b>	39121410
<b>UNSPSC 12.01</b>	39121410
<b>UNSPSC 13.2</b>	39121410

### accessories

#### Ink ribbon

## Insert label - EMT (10X4)R - 0816235

accessories

THERMOMARK-RIBBON 110 - 5145384



---

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>