



| | |
|---|---|
| ITEM-NO. (ITEM-NO.) | 231-651/019-000 |
| Cross section1 (Cross section / mm²) | 0.08 - 2.5 |
| Cross section2 (Cross section / AWG) | 28 - 12 |
| Strip length (Strip length / mm) | 8 - 9 |
| Measured voltage (Measured voltage / V) | 320 |
| Measured shock voltage (Measured shock voltage / kV) | 4 |
| Pollution degree (Pollution degree) | 2 |
| Current intensity (Current intensity / A) | 12 |
| RM (PIN SPACING / mm) | 5.08 |
| P (NO. OF POLES) | 21 |
| Height (Height / mm) | 14.3 |
| Width (Width / mm) | 121.48 |
| Depth (Depth / mm) | 27.5 |
| No. of connection Points (No. of connection Points) | 21 |
| No. of potentials (No. of potentials) | 21 |
| COLOR (COLOR) | orange |
| WEIGHT (WEIGHT / g) | 32.65 |
| Comment (Comment) | A = (No. of poles x Pin Spacing) + 3,2 mm D = A - 0,2 mm E = D + 5,8 mm F = D + 11,8 mm |