

# Multi-level terminal block - PT 1,5/S-3L BU - 3213726

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Multi-level terminal block, Cross section: 0.14 mm<sup>2</sup> - 1.5 mm<sup>2</sup>, AWG: 26 - 16, Connection type: Push-in connection, Width: 3.5 mm, Color: blue, Mounting type: NS 35/7,5, NS 35/15

## Product Features

- The push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- The compact design and front connection enable wiring in a confined space
- In addition to the testing facility in the double function shaft, all terminal blocks provide an additional test connection
- Tested for railway applications

## Key commercial data

package_quantity	50
GTIN	4046356572491

## Technical data

### General

Number of levels	3
Number of connections	6
Color	blue
Insulating material	PA
Inflammability class according to UL 94	V0
Area of application	Railway industry
Area of application	Mechanical engineering
Area of application	Plant engineering

### General

Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I <sub>N</sub>	15 A
Nominal voltage U <sub>N</sub>	500 V
Open side panel	ja

## Dimensions

# Multi-level terminal block - PT 1,5/S-3L BU - 3213726

## Technical data

### Dimensions

<b>Width</b>	3.5 mm
<b>Length</b>	97.2 mm
<b>Height NS 35/7,5</b>	53.2 mm
<b>Height NS 35/15</b>	60.7 mm

### Connection data

<b>Conductor cross section solid min.</b>	0.14 mm <sup>2</sup>
<b>Conductor cross section solid max.</b>	1.5 mm <sup>2</sup>
<b>Conductor cross section stranded min.</b>	0.14 mm <sup>2</sup>
<b>Conductor cross section stranded max.</b>	1.5 mm <sup>2</sup>
<b>Conductor cross section AWG/kcmil min.</b>	26
<b>Conductor cross section AWG/kcmil max</b>	16
<b>Conductor cross section stranded, with ferrule without plastic sleeve min.</b>	0.14 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule without plastic sleeve max.</b>	1.5 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule with plastic sleeve min.</b>	0.14 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule with plastic sleeve max.</b>	1 mm <sup>2</sup>
<b>Connection method</b>	Push-in connection
<b>Stripping length</b>	8 mm
<b>Internal cylindrical gage</b>	A1 / B1

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27141117
<b>eCl@ss 4.1</b>	27141117
<b>eCl@ss 5.0</b>	27141120
<b>eCl@ss 5.1</b>	27141120
<b>eCl@ss 6.0</b>	27141120
<b>eCl@ss 7.0</b>	27141120
<b>eCl@ss 8.0</b>	27141120

### ETIM

<b>ETIM 4.0</b>	EC000897
<b>ETIM 5.0</b>	EC000897

### UNSPSC

<b>UNSPSC 6.01</b>	30211811
<b>UNSPSC 7.0901</b>	39121410
<b>UNSPSC 11</b>	39121410
<b>UNSPSC 12.01</b>	39121410
<b>UNSPSC 13.2</b>	39121410

# Multi-level terminal block - PT 1,5/S-3L BU - 3213726

## approvals

UL Recognized / cUL Recognized / GOST / CSA / GL / LR / GOST / cULus Recognized /

### Approval details

<b>UL Recognized</b>			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	15 A	15 A	5 A
mm <sup>2</sup> /AWG/kcmil	26-14	26-14	26-14

<b>cUL Recognized</b>			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	15 A	15 A	5 A
mm <sup>2</sup> /AWG/kcmil	26-14	26-14	26-14

<b>GOST</b>			
-------------	--	--	--

<b>CSA</b>			
Usegroups	B	C	D
Nominal voltage UN	300 V	300 V	600 V
Nominal current IN	15 A	15 A	5 A
mm <sup>2</sup> /AWG/kcmil	26-14	26-14	26-14


<b>GL</b>			
-----------	--	--	--

<b>LR</b>			
-----------	--	--	--

--	--	--	--

## Multi-level terminal block - PT 1,5/S-3L BU - 3213726

approvals

cULus Recognized  US

accessories

### Screwdriver tools

SZF 0-0,4X2,5 - 1204504



---

### End cover

D-PT 1,5/S-3L - 3113771



---

### Marker carriers

STP 3,5-3 - 0830132



---

### Documentation

PT-IL - 3208090



## Multi-level terminal block - PT 1,5/S-3L BU - 3213726

accessories

### Bridge

FBS 2-3,5 - 3213014



FBS 3-3,5 - 3213027



FBS 4-3,5 - 3213030



FBS 5-3,5 - 3213043



FBS 10-3,5 - 3213056



## Multi-level terminal block - PT 1,5/S-3L BU - 3213726

### accessories

FBS 20-3,5 - 3213069



FBS 2-3,5 BU - 3213086



FBS 3-3,5 BU - 3213099



FBS 4-3,5 BU - 3213109



FBS 5-3,5 BU - 3213112



FBS 10-3,5 BU - 3213125



## Multi-level terminal block - PT 1,5/S-3L BU - 3213726

accessories

---

FBS 20-3,5 BU - 3213138



FBS 1,5/S-PV - 3216263



RB ST 6-1,5/S - 3213250



### Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



## Multi-level terminal block - PT 1,5/S-3L BU - 3213726

### accessories

NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762





## Multi-level terminal block - PT 1,5/S-3L BU - 3213726

accessories

---

NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



## Multi-level terminal block - PT 1,5/S-3L BU - 3213726

### accessories

NS 35/15 AL UNPERF 2000MM - 1201756



---

NS 35/15 ZN PERF 2000MM - 1206599



---

NS 35/15 ZN UNPERF 2000MM - 1206586



---

NS 35/15 CU UNPERF 2000MM - 1201895



---

NS 35/15 CAP - 1206573



---

NS 35/15-2,3 UNPERF 2000MM - 1201798



# Multi-level terminal block - PT 1,5/S-3L BU - 3213726

accessories

---

## Terminal marking

ZB 3,5:UNBEDRUCKT - 0829414



UCT-TM 3,5 - 0829484



ZBF 3,5:UNBEDRUCKT - 0829392



UCT-TMF 3,5 - 0829486



## Labeled terminal marker

ZB 3,5 CUS - 0829415



## Multi-level terminal block - PT 1,5/S-3L BU - 3213726

### accessories

UCT-TM 3,5 CUS - 0829581



ZBF 3,5 CUS - 0829394



UCT-TMF 3,5 CUS - 0829644



### Test plug terminal block

MPS-MT - 0201744



### Insulating sleeve

MPS-IH WH - 0201663



## Multi-level terminal block - PT 1,5/S-3L BU - 3213726

### accessories

MPS-IH RD - 0201676



MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



# Multi-level terminal block - PT 1,5/S-3L BU - 3213726

accessories

---

## Planning and marking software

CLIP-PROJECT ADVANCED - 5146040



CLIP-PROJECT PROFESSIONAL - 5146053



## End block

E/UK - 1201442



E/UK 1 - 1201413



CLIPFIX 35 - 3022218



# Multi-level terminal block - PT 1,5/S-3L BU - 3213726

accessories

CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



## Drawings

Circuit diagram

