Sensor/actuator connector - SACC-M 8MS-3QO-0,25-M - 1441008

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)



Sensor/actuator connector, 3-position, Plug straight M8, A-coded, Insulation displacement connection, Knurl material: Nickel-plated brass, External cable diameter 2.5 mm ... 5 mm

Product Features

- Safe use in the field, thanks to a high degree of protection
- Flexible: connectors for on-site assembly
- Insulation displacement connection: innovative and time-saving assembly without stripping the single wire

Key commercial data

package_quantity	1
GTIN	4046356515894

Technical data

Dimensions

External diameter	2.5 mm ... 5 mm ± 0.2 mm
Stripping length of the sheath	40 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 80 °C (Plug / socket)
Degree of protection	IP65
Degree of protection	IP67

General

Rated current at 40°C	4 A
Rated voltage	60 V
Number of positions	3
Contact resistance	≤ 5 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Standards/regulations	M8 connector IEC 61076-2-104
Status display	No
Surge voltage category	II
Pollution degree	3
Connection method	Insulation displacement connection
Conductor cross section	0.08 mm² ... 0.25 mm²
AWG conductor cross section	28 ... 24

Sensor/actuator connector - SACC-M 8MS-3QO-0,25-M - 1441008

Technical data

General

Wire diameter including insulation	0.75 mm ... 1.5 mm ±0.05 mm
Frequency of connections between conductors of the same cross section	10
Wire insulation material	PVC/PE/PP
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	Class 2-6
Insertion/withdrawal cycles	≥ 100
Torque	0.6 Nm (Pressure nut)
Torque	0.2 Nm (M8 knurl)

Material

Inflammability class according to UL 94	HB
Contact material	CuSn
Contact surface material	Ni/Au
Contact carrier material	TPU GF
Material of grip body	PA 6
Material, knurls	Nickel-plated brass

classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27279221
eCl@ss 7.0	27440104
eCl@ss 8.0	27440104

ETIM

ETIM 2.0	EC001121
ETIM 3.0	EC002062
ETIM 4.0	EC002062
ETIM 5.0	EC002062

UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121413
UNSPSC 11	39121413
UNSPSC 12.01	39121413
UNSPSC 13.2	39121413

Sensor/actuator connector - SACC-M 8MS-3QO-0,25-M - 1441008

approvals

UL Recognized / cUL Recognized / GOST / cULus Recognized /

Approval details

UL Recognized

Nominal voltage UN	29 V
Nominal current IN	4 A
mm²/AWG/kcmil	24

cUL Recognized

Nominal voltage UN	29 V
Nominal current IN	4 A
mm²/AWG/kcmil	24

GOST

cULus Recognized

accessories

Torque tool

TSD 02 SAC - 1208487



Sensor/actuator connector - SACC-M 8MS-3QO-0,25-M - 1441008

accessories

TSD-M 1,2NM - 1212224



Screwdriver tools

SAC BIT M8-D10 - 1208461



TSD-M SAC-BIT ADAPTER - 1212600



Protective cap

PROT-M 8 FS-PA-CHAIN - 1430857



Cable by the meter


SAC-3P-100,0-PUR/0,25 - 1501689



Sensor/actuator connector - SACC-M 8MS-3QO-0,25-M - 1441008


Drawings

Functional drawing



Sensor/actuator connector - SACC-M 8MS-3QO-0,25-M - 1441008


Dimensioned drawing



M8 x 1 male plug, straight version

Sensor/actuator connector - SACC-M 8MS-3QO-0,25-M - 1441008

Schematic diagram



Pin assignment M8 plug, 3-pos., view male side

© Phoenix Contact 2013 - all rights reserved
http://www.phoenixcontact.com