

ⓑ



PLATING ITEM 1	PART-NO.
30µm HARD GOLD over min. 50µm NICKEL	131C10049X
50µm HARD GOLD over min. 50µm NICKEL	131J10049X

NOTES:

1. MATERIAL: COPPER ALLOY
2. PLATING:
ITEM 1: SEE TABLE
ITEM 2: min. 8µm HARD GOLD over 50µm NICKEL
ITEM 3: NICKEL PLATED

Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND	tolerance ISO 2768-m		 dim. in mm		scale: 5:1
	1998	date	name		material: SEE NOTES
	drawn	23.03.	Barcinski		title: HIGH POWER CONTACT MALE SOLDER CUP 40A D-SUB COMBINATION
	appd.	23.03.	Mickenbecker		
	norm				
d-old				dwg no: Inventor 10	DIN-A3
1 x b	A2885	10.12.2007	Sonne		
a	Origin				
rev.	description	date	name	part no: SEE TABLE	