

# Protective conductor double-level terminal block - PTTB 4-PE - 3211854

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Protective conductor double-level terminal block, Cross section: 0.2 mm<sup>2</sup> - 6 mm<sup>2</sup>, AWG: 24 - 10, Connection type: Push-in connection, Width: 6.2 mm, Color: green-yellow, Mounting type: NS 35/7,5, NS 35/15

## Product Features

- The push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- The compact design and front connection enable wiring in a confined space
- In addition to the testing facility in the double function shaft, all terminal blocks provide an additional test connection
- Tested for railway applications

## Key commercial data

<b>package_quantity</b>	50
<b>GTIN</b>	4046356482721

## Technical data

### General

<b>Number of levels</b>	2
<b>Number of connections</b>	4
<b>Color</b>	green-yellow
<b>Insulating material</b>	PA
<b>Inflammability class according to UL 94</b>	V0
<b>Area of application</b>	Railway industry
<b>Area of application</b>	Mechanical engineering
<b>Area of application</b>	Plant engineering
<b>Area of application</b>	Process industry

### General

<b>Rated surge voltage</b>	6 kV
<b>Pollution degree</b>	3
<b>Surge voltage category</b>	III
<b>Insulating material group</b>	I
<b>Connection in acc. with standard</b>	IEC 60947-7-2
<b>Open side panel</b>	ja
<b>Shock protection test specification</b>	DIN EN 50274 (VDE 0660-514):2002-11

# Protective conductor double-level terminal block - PTTB 4-PE - 3211854

## Technical data

### General

<b>Back of the hand protection</b>	guaranteed
<b>Finger protection</b>	guaranteed
<b>Test specification, oscillation, broadband noise</b>	DIN EN 50155 (VDE 0115-200):2008-03
<b>Test spectrum</b>	Service life test category 1, class B, body mounted
<b>Test frequency</b>	$f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$
<b>ASD level</b>	$1.857 \text{ (m/s}^2\text{)}^2\text{/Hz}$
<b>Acceleration</b>	0.8 g
<b>Test duration per axis</b>	5 h
<b>Test directions</b>	X-, Y- and Z-axis
<b>Oscillation, broadband noise test result</b>	Test passed
<b>Test specification, shock test</b>	DIN EN 50155 (VDE 0115-200):2008-03
<b>Shock form</b>	Half-sine
<b>Acceleration</b>	5 g
<b>Shock duration</b>	30 ms
<b>Number of shocks per direction</b>	3
<b>Test directions</b>	X-, Y- and Z-axis (pos. and neg.)
<b>Shock test result</b>	Test passed
<b>Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))</b>	130 °C
<b>Static insulating material application in cold</b>	-60 °C

### Dimensions

<b>Width</b>	6.2 mm
<b>Length</b>	83.5 mm
<b>Height NS 35/7,5</b>	47.5 mm
<b>Height NS 35/15</b>	55 mm

### Connection data

<b>Conductor cross section solid min.</b>	0.2 mm <sup>2</sup>
<b>Conductor cross section solid max.</b>	6 mm <sup>2</sup>
<b>Conductor cross section stranded min.</b>	0.2 mm <sup>2</sup>
<b>Conductor cross section stranded max.</b>	4 mm <sup>2</sup>
<b>Conductor cross section AWG/kcmil min.</b>	24
<b>Conductor cross section AWG/kcmil max</b>	10
<b>Conductor cross section stranded, with ferrule without plastic sleeve min.</b>	0.25 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule without plastic sleeve max.</b>	4 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule with plastic sleeve min.</b>	0.25 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule with plastic sleeve max.</b>	4 mm <sup>2</sup>

# Protective conductor double-level terminal block - PTTB 4-PE - 3211854

## Technical data

### Connection data

2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1 mm <sup>2</sup>
Connection method	Push-in connection
Stripping length	12 mm
Internal cylindrical gage	A4

## classifications

### eCl@ss

eCl@ss 4.0	27141118
eCl@ss 4.1	27141118
eCl@ss 5.0	27141118
eCl@ss 5.1	27141118
eCl@ss 6.0	27141141
eCl@ss 7.0	27141141
eCl@ss 8.0	27141141

### ETIM

ETIM 2.0	EC000901
ETIM 3.0	EC000901
ETIM 4.0	EC000901
ETIM 5.0	EC000901

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

## approvals

ATEX / IECEx / UL Recognized / cUL Recognized / GOST / CSA / GL / LR / VDE Zeichengenehmigung / IECCE CB Scheme / GOST / cULus Recognized /

### Approval details



# Protective conductor double-level terminal block - PTTB 4-PE - 3211854

## approvals

Nominal voltage UN	
Nominal current IN	
mm <sup>2</sup> /AWG/kcmil	0.2-4

<b>IECEX</b>	
Nominal voltage UN	
Nominal current IN	
mm <sup>2</sup> /AWG/kcmil	0.2-4

<b>UL Recognized</b>			
<b>Usegroups</b>	<b>B</b>	<b>C</b>	<b>D</b>
Nominal voltage UN			
Nominal current IN			
mm <sup>2</sup> /AWG/kcmil	24-10	24-10	24-10

<b>cUL Recognized</b>			
<b>Usegroups</b>	<b>B</b>	<b>C</b>	<b>D</b>
Nominal voltage UN			
Nominal current IN			
mm <sup>2</sup> /AWG/kcmil	24-10	24-10	24-10

<b>GOST</b>
-------------

<b>CSA</b>	
Nominal voltage UN	
Nominal current IN	
mm <sup>2</sup> /AWG/kcmil	24-10

<b>GL</b>
-----------

<b>LR</b>
-----------

# Protective conductor double-level terminal block - PTTB 4-PE - 3211854

approvals

<b>VDE Zeichengenehmigung</b>	
Nominal voltage UN	
Nominal current IN	
mm <sup>2</sup> /AWG/kcmil	0.2-4

<b>IECEE CB Scheme</b>	
Nominal voltage UN	
Nominal current IN	
mm <sup>2</sup> /AWG/kcmil	0.2-4



accessories

**End cover**

D-STTB 4 - 3030462



DP PS-6 - 3036738



# Protective conductor double-level terminal block - PTTB 4-PE - 3211854

accessories

## Partition plate

ATP-STTB 4 - 3030747



---

## Marker carriers

STP 5-2 - 0800967



---

## Screwdriver tools

SZF 1-0,6X3,5 - 1204517



---

## Documentation

PT-IL - 3208090



---

## Bridge

# Protective conductor double-level terminal block - PTTB 4-PE - 3211854

## accessories

FBS 20-6 - 3030365



FBS 10-6 - 3030271



FBS 5-6 - 3030349



FBS 4-6 - 3030255



FBS 3-6 - 3030242



# Protective conductor double-level terminal block - PTTB 4-PE - 3211854

accessories

FBS 2-6 - 3030336



---

FBS 50-6 - 3032224



---

## Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



---

NS 35/ 7,5 UNPERF 2000MM - 0801681



---

NS 35/ 7,5 WH PERF 2000MM - 1204119





## Protective conductor double-level terminal block - PTTB 4-PE - 3211854

### accessories

NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



## Protective conductor double-level terminal block - PTTB 4-PE - 3211854

accessories

NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



## Protective conductor double-level terminal block - PTTB 4-PE - 3211854

accessories

NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



# Protective conductor double-level terminal block - PTTB 4-PE - 3211854

accessories

NS 35/15-2,3 UNPERF 2000MM - 1201798



---

## Terminal marking

ZBF 6:UNBEDRUCKT - 0808710



---

UC-TMF 6 - 0818140



---

UCT-TMF 6 - 0828746



---

TMT 6 R - 0816498



---

## Labeled terminal marker

## Protective conductor double-level terminal block - PTTB 4-PE - 3211854

accessories

ZBF 6 CUS - 0825027



UC-TMF 6 CUS - 0824646



UCT-TMF 6 CUS - 0829665



TMT 6 R CUS - 0824488



**Test plug terminal block**

MPS-MT - 0201744



# Protective conductor double-level terminal block - PTTB 4-PE - 3211854

## accessories

PAI-4-FIX-5/6 BU - 3035975



PAI-4-FIX-5/6 OG - 3035974



PAI-4-FIX-5/6 YE - 3035977



PAI-4-FIX-5/6 RD - 3035976



PAI-4-FIX-5/6 GN - 3035978



## Protective conductor double-level terminal block - PTTB 4-PE - 3211854

### accessories

PAI-4-FIX-5/6 BK - 3035980



PAI-4-FIX-5/6 GY - 3035982



PAI-4-FIX-5/6 VT - 3035979



PAI-4-FIX-5/6 BN - 3035981



PS-6 - 3030996



# Protective conductor double-level terminal block - PTTB 4-PE - 3211854

accessories

PS-6/2,3MM RD - 3038736



---

## Insulating sleeve

MPS-IH WH - 0201663



---

MPS-IH RD - 0201676



---

MPS-IH BU - 0201689



---

MPS-IH YE - 0201692





# Protective conductor double-level terminal block - PTTB 4-PE - 3211854

## accessories

MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



ISH 4/0,5 - 3002885



ISH 4/1,0 - 3002898



## Planning and marking software

# Protective conductor double-level terminal block - PTTB 4-PE - 3211854

## accessories

CLIP-PROJECT ADVANCED - 5146040



CLIP-PROJECT PROFESSIONAL - 5146053



## End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276




E/NS 35 N - 0800886



## Drawings

## Protective conductor double-level terminal block - PTTB 4-PE - 3211854

Circuit diagram



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>