


Impedance	50 Ω
Frequency range	0 to 18 GHz
Voltage rating	RG-55. 58. 141. 142. 223. 303: 500 volts peak RG-122. 174. 188. 316. 375: 375 volts peak
VSWR (straight connectors)	RG-55 group: 1.15+0.011(GHz) RG-178 group: 1.20+0.251(GHz)
Contact resistance	Center: 2.0 miliohms Body: 2.0 miliohms Braid to body: 0.5 miliohms
Insulation resistance	5000 MHz
Insertion loss	0.03√f(GHz) dB max

7	Nut	Brass	Gold
6	Gasket	Rubber	Red
5	Ferrule	Brass	Gold
4	Shell	Brass	Gold
3	Insulator	Teflon	White
2	Contact	Brass	Gold
1	Body	Brass	Gold
NO	Description	Material	Finish



736452