



<b>ITEM-NO. (ITEM-NO.)</b>	232-313/026-000
<b>Cross section1 (Cross section)</b>	0.08 - 2.5
<b>Cross section2 (Cross section)</b>	28 - 12
<b>Strip length (Strip length)</b>	8 - 9
<b>Measured voltage (Measured voltage)</b>	320
<b>Measured shock voltage (Measured shock voltage)</b>	4
<b>Pollution degree (Pollution degree)</b>	2
<b>Current intensity (Current intensity)</b>	14
<b>RM (PIN SPACING / mm)</b>	5.08
<b>P (NO. OF POLES)</b>	13
<b>Height (Height)</b>	23.9
<b>Width (Width)</b>	68.44
<b>Depth (Depth)</b>	22.75
<b>No. of connection Points (No. of connection Points)</b>	13
<b>No. of potentials (No. of potentials)</b>	13
<b>COLOR (COLOR)</b>	orange
<b>Comment (Comment)</b>	$L = (\text{No. of poles} \times \text{Pin Spacing}) + 1,5 \text{ mm} + 0,9 \text{ mm}$
<b>Dimensions (Dimensions)</b>	