


## Data sheet | Item number: 232-832/047-000

THT female header; 0.6 x 1.0 mm solder pin; angled; Spacer flange; Pin spacing 7.5 mm; 2-pole




[www.wago.com/232-832/047-000](http://www.wago.com/232-832/047-000)



RoHS Compliant

BOMcheck.net

Color:



### Item description

- Horizontal or vertical PCB mounting via straight or angled solder pins
- For board-to-board and board-to-wire connections
- Touch-proof PCB outputs
- Easy-to-identify PCB inputs and outputs
- With coding fingers

Other variants can be requested via the WAGO sales department or, if necessary, configured at <https://configurator.wago.com/>: 3.8 mm pin projection for male headers with straight solder pins, Gold-plated or partially gold-plated contact surfaces, Other pole numbers

### Data

#### Electrical data

#### Ratings per IEC/EN 60664-1

Rated voltage (III / 3)

500 V



|                                 |   |
|---------------------------------|---|
| Rated impulse voltage (III / 3) | 6 kV  |
| Rated voltage (III / 2)         | 630 V   |
| Rated impulse voltage (III / 2) | 6 kV  |
| Rated voltage (II / 2)          | 1000 V  |
| Rated impulse voltage (II / 2)  | 6 kV  |
| Rated current                   | 12 A  |
| Legend (ratings)                | (III / 2) $\hat{=}$ Overvoltage category III / Pollution degree 2 |

### Approvals per UL 1059

|                                |       |
|--------------------------------|-------|
| Rated voltage UL (Use Group B) | 300 V |
| Rated current UL (Use Group B) | 15 A  |
| Rated voltage UL (Use Group D) | 300 V |
| Rated current UL (Use Group D) | 10 A  |

### Approvals per CSA

|                                 |       |
|---------------------------------|-------|
| Rated voltage CSA (Use Group B) | 300 V |
| Rated current CSA (Use Group B) | 15 A  |
| Rated voltage CSA (Use Group D) | 300 V |
| Rated current CSA (Use Group D) | 10 A  |

### Connection data

|                            |   |
|----------------------------|---|
| No. of poles               | 2 |
| Total number of potentials | 2 |
| Number of levels           | 1 |

### Geometrical Data

|                                   |                          |
|-----------------------------------|--------------------------|
| Pin spacing                       | 7.5 mm (0.295 inch)      |
| Width                             | 27.3 mm / 1.075 inch     |
| Height                            | 16.6 mm / 0.654 inch     |
| Height from the surface           | 11.6 mm / 0.457 inch     |
| Depth                             | 18.25 mm / 0.719 inch    |
| Solder pin length                 | 5 mm                     |
| Solder pin dimensions             | 0.6 x 1 mm               |
| Drilled hole diameter (tolerance) | 1.3 <sup>(+0.1)</sup> mm |

### Mechanical data

|                  |                                  |
|------------------|----------------------------------|
| Mounting type    | Mounting flange                  |
| Type of mounting | Flush mounting<br>Panel mounting |

## Plug connection

|                                    |                         |
|------------------------------------|-------------------------|
| Contact type (pluggable connector) | Female connector/socket |
| Connector connection type          | for PCBs                |
| Mismating protection               | No                      |
| Mating direction to the PCB        | 0°                      |

## PCB contact

|                                     |   |
|-------------------------------------|---|
| PCB contact                         | THT                                       |
| Solder pin arrangement              | over the entire female connector, in line |
| Number of solder pins per potential | 1   |

## Material Data

|                             |                      |
|-----------------------------|----------------------|
| Color                       | gray                 |
| Material group              | I                    |
| Insulating material         | Polyamide 66 (PA 66) |
| Flammability class per UL94 | V0                   |
| Contact material            | Copper alloy         |
| Contact plating             | tin-plated           |
| Fire load                   | 0.067 MJ             |
| Weight                      | 3.038 g              |

## Environmental Requirements



|                         |                |
|-------------------------|----------------|
| Limit temperature range | -60 ... +85 °C |
|-------------------------|----------------|

## Commercial data

|                    |                        |
|--------------------|------------------------|
| Country of origin  | DE                     |
| GTIN               | 4044918626217          |
| Customs Tariff No. | 85366990990            |
| Product Group      | 3 (Multi Conn. System) |

## Approvals / Certificates




### Ship Approvals

| Logo   | Approval  | Certificate name |
|--|---|------------------|
|  | <b>ABS</b><br>American Bureau of Shipping               | 14-HG1241537-PDA |
|  | <b>DNV GL</b><br>Det Norske Veritas, Germanischer Lloyd | TAE000016Z       |


### UL-Approvals

| Logo   | Approval                             | Certificate name |
|--|--------------------------------------|------------------|
|  | UR<br>Underwriters Laboratories Inc. | E45172           |
|  | UR<br>Underwriters Laboratories Inc. | E45171           |

### Compatible products

| check   |   |  |
|---|---|--|
|   | Item no.: 210-136<br>Test plug; 2 mm Ø; with 500 mm cable                                 | <a href="http://www.wago.com/210-136">www.wago.com/210-136</a> |
|   | Item no.: 210-137<br>Test plug; 2.3 mm Ø; with 500 mm cable                               | <a href="http://www.wago.com/210-137">www.wago.com/210-137</a> |
|  | Item no.: 231-662<br>Test plugs for female connectors; for 7.5 mm and 7.62 mm pin spacing | <a href="http://www.wago.com/231-662">www.wago.com/231-662</a> |

### Marking accessories

|  |   |  |
|--|---|--|
|  | Item no.: 210-833<br>Marking strips; on reel; 6 mm wide; plain; Self-adhesive | <a href="http://www.wago.com/210-833">www.wago.com/210-833</a> |
|  | Item no.: 210-834<br>Marking strips; on reel; 5 mm wide; plain; Self-adhesive | <a href="http://www.wago.com/210-834">www.wago.com/210-834</a> |

### Downloads

#### smartDATA

#### PCB libraries

|  |                      |               |          |
|--|----------------------|---------------|----------|
| DesignSpark Library for WAGO Pluggable PCB Connectors (MULTI CONNECTION SYSTEM)<br>Compatible with DesignSpark PCB Version 4.x or higher     | 2.1<br>Oct 6, 2014   | ZIP<br>6.1 MB | Download |
| TARGET Library for WAGO Pluggable PCB Connectors (Multi-Connection System)<br>Compatible with TARGET PCB Design Software Version 17.x        | 1.1.0<br>Oct 6, 2014 | ZIP<br>7.4 MB | Download |
| EAGLE Library for WAGO Pluggable PCB Connectors (MULTI CONNECTION SYSTEM)<br>Compatible with EAGLE PCB Design Software Version 6.x or higher | 2.1<br>Nov 17, 2017  | ZIP<br>6.2 MB | Download |



Subject to changes.

---

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.