

Patch panels - VS-PP-F-RJ45-CAT6 - 1658118

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Patch panel, RJ45, DIN rail mounting, IP20, 1 slot, IDC connection, CAT6

Ethernet **PROFIBUS**
NET

Key commercial data

package_quantity	1
GTIN	4046356149174

Technical data

Mechanical characteristics

Number of positions	8
Number of slots	1
Shielded	Yes
Insertion/withdrawal cycles	≥ 750
Connection method	IDC fast connection
Conductor cross section	0.2 mm² ... 0.32 mm²
Connection cross section AWG	24 ... 22
External cable diameter	4.5 mm ... 8 mm
Color	gray

Ambient conditions

Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Degree of protection	IP20

Material data

Inflammability class according to UL 94	V0
Housing material	PC-GF
Contact carrier material	PC
Contact material	Copper alloy
Contact surface material	Gold over nickel

Electrical characteristics

Number of positions	8
Transmission characteristics (category)	CAT6

Patch panels - VS-PP-F-RJ45-CAT6 - 1658118

Technical data

Electrical characteristics

Rated current	1 A
---------------	-----

classifications

eCl@ss

eCl@ss 4.0	272607XX
eCl@ss 4.1	27260701
eCl@ss 5.0	19030109
eCl@ss 5.1	19030109
eCl@ss 6.0	19170107
eCl@ss 7.0	19170112
eCl@ss 8.0	19170112

ETIM

ETIM 3.0	EC001128
ETIM 4.0	EC001128
ETIM 5.0	EC001128


UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

Drawings

Patch panels - VS-PP-F-RJ45-CAT6 - 1658118

Dimensioned drawing



RJ45 patch panel

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>