








No. of pos.	A -0,76	B -0,25	C	D -0,3
9	31,19	16,46	25,00 +0,12 -0,10	6,12
15	39,52	24,79	33,30 +0,15	6,12
25	53,42	38,50	47,04 ± 0,13	5,99
37	69,70	54,96	63,50 +0,13 -0,11	5,99

NOTES:

1. METALSHELLS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
2. TPE ETHYLENE PROPYLENE THERMOPLASTIC RUBBER SEAL
3. IP RATING: THE WATER RESISTANT CAP MUST BE MOUNTED PROPERLY TO THE MATING CONNECTOR FOR IP 67
4. THREADED INSERT: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
5. COLLAR: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
6. (b) JACKSCREW: STAINLESS STEEL 1.4305
7. WIRE ROPE: STAINLESS STEEL 1.4401
8. RETAINING WASHER: STAINLESS STEEL 1.4122
9. TERMINAL RING: UNINSULATED, COPPER ALLOY; min. 200µinTIN over 80µin NICKEL
10. MAXIMUM TORQUE VALUE FOR THREAD: 6in.LB
11. CONNECTOR IS PART MARKED: PART NO. CONEC ABC

Directive 2002/95/EC „RoHS" Compliant

©

Part No. for plug connector		
No.of pos.	UNC 4-40	M 3
9	15-000110	15-000160
15	15-000120	15-000170
25	15-000130	15-000180
37	15-000140	15-000190

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL

CUSTOMER APPROVAL DATE:

NAME: TITLE:

COMPANY NAME:

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
1 x c	Ä 3182	10.11.08	Petker
1 x b	Ä3023	28.05.08	Petker
a	Origin		

tolerance — dim. in mm

	date	name
drawn	02.05.08	Sonnenberg
appd.	02.05.08	Fischer
norm		
d-old		

scale: 2:1 (5:1)

material: SEE NOTES

title:

WATER RESISTANT SCREEN CAP

9-37pos. FOR PLUG CONNECTOR

with threaded insert, jackscrew and wire rope

dwg no: 15K1A218 | Inventor 10 | DIN-A3 | sh: 1

part no: see table