



SPECIFICATIONS


Current Rating: 3A AC, DC
 Voltage Rating: 250V AC/DC
 Contact Resistance: 20m Ω Max
 Insulation Resistance: 1000M Ω Min
 Withstanding Voltage: 1000V AC for 1 minute
 Temperature Range: -40°C to +105°C
 Contact : Copper Alloy
 Insulator: PBT+G.F., UL94V-0
 Shell: Steel

ORDER INFORMATION




V	S	X	1	-	M	XX	X	X	X
D-SUB Type	Solder Type	PBT		Male	N:Nickel Shell T:Tin Shell	W:White Insulator B:Black Insulator	A:Non Accessories B:Front Rivet #4-40, Height=5,8 C:Front Rivet M3, Height=5,8 D:Rear Rivet #4-40, Height=5,8 E:Rear Rivet M3, Height=5,8		
				No. of Contacts					
G0:Gold Flash		S0:Selective Flash							
G1:Gold 3u"		S1:Selective 3u"							
G2:Gold 5u"		S2:Selective 5u"							
G3:Gold 10u"		S3:Selective 10u"							
G4:Gold 15u"		S4:Selective 15u"							
G5:Gold 30u"		S5:Selective 30u"							



Positions	A±0.2	B±0.2	C±0.3	D
9	17.90	24.99	30.80	16.33
15	26.50	33.32	39.14	24.66
25	40.00	47.04	53.04	38.38
37	56.50	63.50	69.32	54.84



50pin



		PART NO.		VSX1-MXXXXX		DRAWN		Andrew	
		DRAWING NO.		VSX1-MXXXXX		CHECKED		Claudia	
		DATE		2016/12/13		APPROVED		Brian	
TITLE: D-SUB Solder type		REV. A0	TOLERANCE	.X ±0.25 .XX ±0.20	SCALE	1:1		UNIT	mm