


## Product information

### Field Attachable M12 Connectors - Standard Type - RSC 5/9

Industrial Connecting Solutions: Circular Connectors: M8 - M12 Connectors: M12 Connectors: M12 Circular connector acc. to IEC 61076-2-101: M12 Field Attachable Connectors: Field Attachable M12

#### Connectors - Standard Type

[http://www.e-catalog.beldensolutions.com/link/57078-24228-256281-256292-256304-58429-58478-58928/en/RSC6\\_5-9/ui/state](http://www.e-catalog.beldensolutions.com/link/57078-24228-256281-256292-256304-58429-58478-58928/en/RSC6_5-9/ui/state)

Name	
Field Attachable M12 Connectors - Standard Type	
	
Field attachable connector, M12 male connector, straight version, with threaded joint, assembling with screw terminals	
Delivery informations	
Availability	available
Product description	
Type	RSC 5/9
Order No.	11591
Description	Field attachable connector, M12 male connector, straight version, with threaded joint, assembling with screw terminals
Color of housing	black
Classification	
Belden brand	Lumberg-Automation
Eclass-ID	27260702
Mechanical data	
Type of plug-in contact	Male connector
Design of housing	straight
LED display present	✘
Connectable conductor cross-section multiple wire (without sleeve)	max. 0.75 mm <sup>2</sup>
Screw joint for cable for external cable diameter	4.0 mm ... 8.0 mm
Screwed cable gland, connecting thread	SW 19
Environmental conditions	
Environmental temperature	-25 °C ... 90 °C
Degree of protection (IP), mounted	IP67
Pollution degree	3
Materials	
Housing material / Molded body	PBT
Contact bearer material	PBT
Contact material	CuZn
Contact material - Surface refinement	pre-coppered, CuSnZn
Knurled screw / nut material	CuZn, nickel-plated
Sealing material	FKM
Electrical data	
Contact resistance	≤ 5 mΩ
Rated current I <sub>n</sub>	4 A at 40°C, UL and notice derating
Nominal voltage	60 V
Rated voltage (Value)	63 V
Test voltage	1.5 kV eff./60 s
Insulation resistance	> 1 GΩ
Approvals	
Approvals	UL

**Belden Deutschland GmbH**

Im Gewerbepark 2  
58579 Schalksmühle  
Germany  
Phone: +49 7127/14-1806  
E-Mail: [icos-sales@belden.com](mailto:icos-sales@belden.com)

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.