

N disconnect terminal block - UTN 6 - 3245037

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



N disconnect terminal block, Screw connection, Cross section: 0.2 mm² - 10 mm², AWG: 24 - 8, Width: 8.2 mm, Color: blue, Mounting type: NS 35/7,5, NS 35/15

Product Features

- Same shape as UT standard terminal blocks

Key commercial data

package_quantity	50
GTIN	4046356299022

Technical data

General

Note	Assembly instructions:For secure fastening of the neutral busbar, supports must be set at the beginning and end of each terminal strip as well as every 20 cm on longer terminal strips.
Number of levels	1
Number of connections	1
Color	blue
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	41 A
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	41 A
Nominal voltage U _N	400 V
Open side panel	ja
Shock protection test specification	DIN EN 50274 (VDE 0660-514):2002-11
Back of the hand protection	guaranteed
Finger protection	guaranteed
Surge voltage test setpoint	7.3 kV

N disconnect terminal block - UTN 6 - 3245037

Technical data

General

Result of surge voltage test	Test passed
Power frequency withstand voltage setpoint	1.89 kV
Result of power-frequency withstand voltage test	Test passed
Checking the mechanical stability of terminal points (5 x conductor connection)	Test passed
Bending test conductor cross section/weight	0.2 mm ² / 0.2 kg
Bending test conductor cross section/weight	6 mm ² / 1.4 kg
Bending test conductor cross section/weight	10 mm ² / 2 kg
Result of bending test	Test passed
Conductor cross section tensile test	0.2 mm ²
Tractive force setpoint	10 N
Conductor cross section tensile test	6 mm ²
Tractive force setpoint	80 N
Conductor cross section tensile test	10 mm ²
Tractive force setpoint	90 N
Tensile test result	Test passed
Tight fit on carrier	NS 35
Setpoint	5 N
Result of tight fit test	Test passed
Result of voltage drop test	Test passed
Temperature-rise test	Test passed
Conductor cross section short circuit testing	6 mm ²
Short-time current	0.72 kA
Short circuit stability result	Test passed
Ageing test for screwless modular terminal block temperature cycles	192
Result of aging test	Test passed
Proof of thermal characteristics (needle flame) effective duration	30 s
Result of thermal test	Test passed
Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))	120 °C

Dimensions

Width	8.2 mm
Length	55 mm
Height NS 35/7,5	47.5 mm

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	10 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	8
Conductor cross section stranded min.	0.2 mm ²

N disconnect terminal block - UTN 6 - 3245037

Technical data

Connection data

Conductor cross section stranded max.	10 mm ²
Min. AWG conductor cross section, stranded	24
Max. AWG conductor cross section, stranded	8
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	6 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	6 mm ²
2 conductors with same cross section, solid min.	0.2 mm ²
2 conductors with same cross section, solid max.	2.5 mm ²
2 conductors with same cross section, stranded min.	0.2 mm ²
2 conductors with same cross section, stranded max.	2.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	4 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm ²
Connection method	Screw connection
Stripping length	10 mm
Screw thread	M 4
Tightening torque, min	1.5 Nm
Tightening torque max	1.8 Nm

classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000902
ETIM 5.0	EC000902

N disconnect terminal block - UTN 6 - 3245037

classifications

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

GOST /

Approval details



accessories

Neutral conductor rail

NLS-CU 3/10 SN 1000MM - 0402174



NLS-CU 3/10 SN 1000MM - 0402174



Pick-off terminal block

EK 135 - 0401023



N disconnect terminal block - UTN 6 - 3245037

accessories

EK 116 - 0401010



Support

UAB - 3032428



AB/NS - 1201141



AB-UTN 2,5/10 - 3245082



Screwdriver tools

SZS 1,0X4,0 VDE - 1205066



Partition plate

N disconnect terminal block - UTN 6 - 3245037

accessories

ATP-UT - 3047167



Bridge

FBS 2-8 - 3030284



FBS 3-8 - 3030297



FBS 4-8 - 3030307



FBS 5-8 - 3030310



N disconnect terminal block - UTN 6 - 3245037

accessories

FBS 10-8 - 3030323



FBSRH 2-8 - 3033802



FBSRH 3-8 - 3033803



FBSRH 4-8 - 3033804



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



N disconnect terminal block - UTN 6 - 3245037

accessories

NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



N disconnect terminal block - UTN 6 - 3245037

accessories

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



N disconnect terminal block - UTN 6 - 3245037

accessories

NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



N disconnect terminal block - UTN 6 - 3245037

accessories

NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZB 8:UNBEDRUCKT - 1052002



UC-TM 8 - 0818072



UCT-TM 8 - 0828740



Labeled terminal marker

ZB 8 CUS - 0825011



N disconnect terminal block - UTN 6 - 3245037

accessories

UC-TM 8 CUS - 0824597



UCT-TM 8 CUS - 0829616



Test plug terminal block

MPS-MT - 0201744



PAI-4-FIX BU - 3032729



PAI-4-FIX OG - 3034455



N disconnect terminal block - UTN 6 - 3245037

accessories

PAI-4-FIX YE - 3032745



PAI-4-FIX RD - 3032732



PAI-4-FIX GN - 3032758



PAI-4-FIX BK - 3032774



PAI-4-FIX GY - 3032790



PAI-4-FIX VT - 3032761



N disconnect terminal block - UTN 6 - 3245037

accessories

PAI-4-FIX BN - 3032787



PS-8 - 3031005



PS-8/2,3MM RD - 3048564



Insulating sleeve

MPS-IH WH - 0201663



MPS-IH RD - 0201676



N disconnect terminal block - UTN 6 - 3245037

accessories

MPS-IH BU - 0201689



MPS-IH YE - 0201692



MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



End cover

N disconnect terminal block - UTN 6 - 3245037

accessories

DP PS-8 - 3036741



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



E/UK - 1201442



N disconnect terminal block - UTN 6 - 3245037

accessories

E/UK 1 - 1201413



Drawings

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>