

Feed-through terminal block - MBKKB 2,5 - 1414064

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Cross section: 0.2 mm² - 4 mm², AWG: 24 - 12, Connection type: Screw connection, Width: 5.2 mm, Color: gray, Mounting type: NS 15

Product Features

- Fixed bridges and test sockets can be used on both levels
- Space saving thanks to compact design and mounting option on a 15 mm DIN rail
- Clear arrangement thanks to marking of all terminal points
- Easy potential distribution thanks to standardized plug-in bridges



Key commercial data

package_quantity	50
GTIN	4017918021313

Technical data

General

Number of levels	2
Number of connections	4
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V2

General

Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	24 A
Nominal voltage U _N	500 V
Open side panel	ja
Shock protection test specification	DIN EN 50274 (VDE 0660-514):2002-11
Back of the hand protection	guaranteed

Feed-through terminal block - MBKKB 2,5 - 1414064

Technical data

General

Finger protection	guaranteed
Surge voltage test setpoint	7.3 kV
Result of surge voltage test	Test passed
Power frequency withstand voltage setpoint	1.89 kV
Result of power-frequency withstand voltage test	Test passed
Checking the mechanical stability of terminal points (5 x conductor connection)	Test passed
Bending test rotation speed	10 rpm
Bending test turns	135
Bending test conductor cross section/weight	0.2 mm ² / 0.2 kg
Bending test conductor cross section/weight	2.5 mm ² / 0.7 kg
Bending test conductor cross section/weight	4 mm ² / 0.9 kg
Result of bending test	Test passed
Conductor cross section tensile test	0.2 mm ²
Tractive force setpoint	10 N
Conductor cross section tensile test	2.5 mm ²
Tractive force setpoint	50 N
Conductor cross section tensile test	4 mm ²
Tractive force setpoint	60 N
Tensile test result	Test passed
Tight fit on carrier	NS 35/NS 15
Setpoint	1 N
Result of tight fit test	Test passed
Requirements, voltage drop	≤ 3.2 mV
Result of voltage drop test	Test passed
Temperature-rise test	Test passed
Conductor cross section short circuit testing	2.5 mm ²
Short-time current	0.3 kA
Short circuit stability result	Test passed
Proof of thermal characteristics (needle flame) effective duration	30 s
Result of thermal test	Test passed
Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))	125 °C

Dimensions

Width	5.2 mm
Length	62 mm
Height NS 35/7,5	48 mm
Height NS 35/15	55.5 mm

Connection data

Conductor cross section solid min.	0.2 mm ²
------------------------------------	---------------------

Feed-through terminal block - MBKKB 2,5 - 1414064

Technical data

Connection data

Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	2.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.25 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	1.5 mm ²
2 conductors with same cross section, solid min.	0.2 mm ²
2 conductors with same cross section, solid max.	1.5 mm ²
2 conductors with same cross section, stranded min.	0.2 mm ²
2 conductors with same cross section, stranded max.	1.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	1.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1 mm ²
Cross section with insertion bridge, solid max.	2.5 mm ²
Cross section with insertion bridge, stranded max.	2.5 mm ²
Connection method	Screw connection
Stripping length	7 mm
Internal cylindrical gage	A3
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

classifications

eCl@ss

eCl@ss 4.0	27141118
eCl@ss 4.1	27141118
eCl@ss 5.0	27141118
eCl@ss 5.1	27141118
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

Feed-through terminal block - MBKKB 2,5 - 1414064

classifications

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC


UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410


approvals

IECEX / ATEX / CSA / UL Recognized / cUL Recognized / GOST / LR / GL / BV / DNV / RS / PRS / GOST / LR / cULus Recognized /

Approval details

IECEX	
Nominal voltage UN	275 V
Nominal current IN	21 A
mm ² /AWG/kcmil	0.2-2.5

ATEX 	
Nominal voltage UN	275 V
Nominal current IN	21 A
mm ² /AWG/kcmil	0.2-2.5

CSA 	
Nominal voltage UN	300 V
Nominal current IN	20 A
mm ² /AWG/kcmil	28-12

Feed-through terminal block - MBKKB 2,5 - 1414064

approvals

UL Recognized	
Nominal voltage UN	300 V
Nominal current IN	20 A
mm ² /AWG/kcmil	30-12

cUL Recognized	
Nominal voltage UN	300 V
Nominal current IN	20 A
mm ² /AWG/kcmil	30-12

GOST

LR	
Nominal voltage UN	800 V
Nominal current IN	57 A
mm ² /AWG/kcmil	10

GL

BV

DNV

RS

PRS


--

--

Feed-through terminal block - MBKKB 2,5 - 1414064

approvals

Nominal voltage UN	500 V
Nominal current IN	24 A
mm ² /AWG/kcmil	2.5



accessories

Partition plate

DP-MBKKB 2,5 - 1413065



TS-KK 3 SO - 2778534



End cover

D-MBKKB 2,5 - 1413052



Bridge

FB-150 METER - 0201595



Feed-through terminal block - MBKKB 2,5 - 1414064

accessories

FBRNI 2-5 N - 3000175



FBRNI 3-5 N - 3000162



FBRNI 4-5 N - 3000159



FBRNI 10-5 N - 2770639



FBRNI 20-5 N - 3000609



Feed-through terminal block - MBKKB 2,5 - 1414064

accessories

EB 2- 5 - 1401158



EB 3- 5 - 1401145



EB 10- 5 - 1401132



SBRN 2-7 - 1413230



Test plug terminal block

RPS - 0201647



Terminal marking

Feed-through terminal block - MBKKB 2,5 - 1414064

accessories

SBS 5:UNBEDRUCKT - 1007219



ZB 5 :UNBEDRUCKT - 1050004



UC-TM 5 - 0818108



UCT-TM 5 - 0828734



Screwdriver tools

SZS 0,6X3,5 - 1205053



Mounting rail

Feed-through terminal block - MBKKB 2,5 - 1414064

accessories

NS 15 UNPERF 2000MM - 1401695



NS 15 PERF 2000MM - 1401682



NS 15 AL PERF 2000MM - 1401763



NS 15 WH PERF 2000MM - 1204096



NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



Feed-through terminal block - MBKKB 2,5 - 1414064

accessories

NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



Feed-through terminal block - MBKKB 2,5 - 1414064

accessories

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



Feed-through terminal block - MBKKB 2,5 - 1414064

accessories

NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



Feed-through terminal block - MBKKB 2,5 - 1414064

accessories

NS 35/15-2,3 UNPERF 2000MM - 1201798



Labeled terminal marker

ZB 5 CUS - 0824962



UC-TM 5 CUS - 0824581



UCT-TM 5 CUS - 0829595



End block

CLIPFIX 35 - 3022218



Feed-through terminal block - MBKKB 2,5 - 1414064

accessories

CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



E/MBK - 1401637



E/MK - 1421633



E/MK 1 - 1421659



E/UK - 1201442



Feed-through terminal block - MBKKB 2,5 - 1414064

accessories

E/UK 1 - 1201413



Test socket

PSBJ 3/13/4 - 0201304



PSB 3/10/4 - 0601292




Drawings

Feed-through terminal block - MBKKB 2,5 - 1414064

Circuit diagram



Circuit diagram



1 = cover
 2 = spacer plate
 3 = fixed bridge
 4 = insertion bridge
 5 = separating plate
 6 = test plug sockets, for test connection with test plug MPS or adapter plug RPS
 7 = test plug sockets, insulated, can only be used for FBRNI

