

# Feed-through terminal block - PT 4-QUATTRO - 3211797

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Push-in connection, Cross section: 0.2 mm<sup>2</sup> - 6 mm<sup>2</sup>, AWG: 24 - 10, Width: 6.2 mm, Height: 35.3 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/15

## Product Features

- The push-in connection terminal blocks are characterized by the system features of the CLIPLINE complete system and by easy and tool-free wiring of conductors with ferrules or solid conductors
- The compact design and front connection enable wiring in a confined space
- In addition to the testing facility in the double function shaft, all terminal blocks provide an additional test connection
- Tested for railway applications

## Key commercial data

package_quantity	50
GTIN	4046356482660

## Technical data

### General

Note	The max. load current must not be exceeded by the total current of all connected conductors.
Number of levels	1
Number of connections	4
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0
Area of application	Railway industry
Area of application	Mechanical engineering
Area of application	Plant engineering
Area of application	Process industry

### General

Maximum load current	38 A (In the case of a 6 mm <sup>2</sup> conductor cross section, the maximum load current must not be exceeded by the total current of all connected conductors)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I

# Feed-through terminal block - PT 4-QUATTRO - 3211797

## Technical data

### General

Connection in acc. with standard	IEC 60947-7-1
Nominal current $I_N$	32 A (In the case of a 6 mm <sup>2</sup> conductor cross section, the maximum load current must not be exceeded by the total current of all connected conductors)
Nominal voltage $U_N$	800 V
Open side panel	ja
Shock protection test specification	DIN EN 50274 (VDE 0660-514):2002-11
Back of the hand protection	guaranteed
Finger protection	guaranteed
Surge voltage test setpoint	9.8 kV
Result of surge voltage test	Test passed
Power frequency withstand voltage setpoint	2 kV
Result of power-frequency withstand voltage test	Test passed
Checking the mechanical stability of terminal points (5 x conductor connection)	Test passed
Bending test rotation speed	10 rpm
Bending test turns	135
Bending test conductor cross section/weight	0.2 mm <sup>2</sup> / 0.2 kg
Bending test conductor cross section/weight	4 mm <sup>2</sup> / 0.9 kg
Bending test conductor cross section/weight	6 mm <sup>2</sup> / 1.4 kg
Result of bending test	Test passed
Conductor cross section tensile test	0.2 mm <sup>2</sup>
Tractive force setpoint	10 N
Conductor cross section tensile test	4 mm <sup>2</sup>
Tractive force setpoint	60 N
Conductor cross section tensile test	6 mm <sup>2</sup>
Tractive force setpoint	80 N
Tensile test result	Test passed
Tight fit on carrier	NS 35
Setpoint	1 N
Result of tight fit test	Test passed
Requirements, voltage drop	≤ 3.2 mV
Result of voltage drop test	Test passed
Temperature-rise test	Test passed
Conductor cross section short circuit testing	4 mm <sup>2</sup>
Short-time current	0.48 kA
Conductor cross section short circuit testing	6 mm <sup>2</sup>
Short-time current	0.72 kA
Short circuit stability result	Test passed
Ageing test for screwless modular terminal block temperature cycles	192
Result of aging test	Test passed

# Feed-through terminal block - PT 4-QUATTRO - 3211797

## Technical data

### General

<b>Proof of thermal characteristics (needle flame) effective duration</b>	30 s
<b>Result of thermal test</b>	Test passed
<b>Test specification, oscillation, broadband noise</b>	DIN EN 50155 (VDE 0115-200):2008-03
<b>Test spectrum</b>	Service life test category 1, class B, body mounted
<b>Test frequency</b>	$f_1 = 5 \text{ Hz}$ to $f_2 = 150 \text{ Hz}$
<b>ASD level</b>	$1.857 \text{ (m/s}^2\text{)}^2\text{/Hz}$
<b>Acceleration</b>	0.8 g
<b>Test duration per axis</b>	5 h
<b>Test directions</b>	X-, Y- and Z-axis
<b>Oscillation, broadband noise test result</b>	Test passed
<b>Test specification, shock test</b>	DIN EN 50155 (VDE 0115-200):2008-03
<b>Shock form</b>	Half-sine
<b>Acceleration</b>	5 g
<b>Shock duration</b>	30 ms
<b>Number of shocks per direction</b>	3
<b>Test directions</b>	X-, Y- and Z-axis (pos. and neg.)
<b>Shock test result</b>	Test passed
<b>Temperature index, insulating material (DIN EN 60216-1 (VDE 0304-21))</b>	130 °C
<b>Static insulating material application in cold</b>	-60 °C

### Dimensions

<b>Width</b>	6.2 mm
<b>Length</b>	77 mm
<b>Height</b>	35.3 mm
<b>Height NS 35/7,5</b>	36.5 mm
<b>Height NS 35/15</b>	44 mm

### Connection data

<b>Conductor cross section solid min.</b>	0.2 mm <sup>2</sup>
<b>Conductor cross section solid max.</b>	6 mm <sup>2</sup>
<b>Conductor cross section AWG/kcmil min.</b>	24
<b>Conductor cross section AWG/kcmil max</b>	10
<b>Conductor cross section stranded min.</b>	0.2 mm <sup>2</sup>
<b>Conductor cross section stranded max.</b>	4 mm <sup>2</sup>
<b>Min. AWG conductor cross section, stranded</b>	24
<b>Max. AWG conductor cross section, stranded</b>	12
<b>Conductor cross section stranded, with ferrule without plastic sleeve min.</b>	0.25 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule without plastic sleeve max.</b>	4 mm <sup>2</sup>
<b>Conductor cross section stranded, with ferrule with plastic sleeve min.</b>	0.25 mm <sup>2</sup>

# Feed-through terminal block - PT 4-QUATTRO - 3211797

## Technical data

### Connection data

Conductor cross section stranded, with ferrule with plastic sleeve max.	4 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1 mm <sup>2</sup>
Connection method	Push-in connection
Minimum stripping length	8 mm
Maximum stripping length	10 mm
Internal cylindrical gage	A4

## classifications

### eCl@ss

eCl@ss 4.0	27141121
eCl@ss 4.1	27141121
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

### ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

### UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

## approvals

---


ATEX / IECEx / UL Recognized / cUL Recognized / GOST / CSA / GL / LR / VDE Gutachten mit Fertigungsüberwachung / IECCEB CB Scheme / GOST / cULus Recognized /

---


## Approval details


# Feed-through terminal block - PT 4-QUATTRO - 3211797


## approvals


<b>ATEX</b> 	
Nominal voltage UN	550 V
Nominal current IN	28 A
mm <sup>2</sup> /AWG/kcmil	0.2-4

<b>IECEX</b>	
Nominal voltage UN	550 V
Nominal current IN	28 A
mm <sup>2</sup> /AWG/kcmil	0.2-4

<b>UL Recognized</b> 		
<b>Usegroups</b>	<b>B</b>	<b>C</b>
Nominal voltage UN	600 V	600 V
Nominal current IN	30 A	30 A
mm <sup>2</sup> /AWG/kcmil	24-10	24-10

<b>cUL Recognized</b> 		
<b>Usegroups</b>	<b>B</b>	<b>C</b>
Nominal voltage UN	600 V	600 V
Nominal current IN	30 A	30 A
mm <sup>2</sup> /AWG/kcmil	24-10	24-10

<b>GOST</b> 	
---	--


<b>CSA</b> 		
<b>Usegroups</b>	<b>B</b>	<b>C</b>
Nominal voltage UN	600 V	600 V
Nominal current IN	30 A	30 A
mm <sup>2</sup> /AWG/kcmil	24-10	24-10

# Feed-through terminal block - PT 4-QUATTRO - 3211797


approvals

GL


LR


VDE Gutachten mit Fertigungsüberwachung 

Nominal voltage UN	800 V
Nominal current IN	32 A
mm <sup>2</sup> /AWG/kcmil	0.2-4

IECEE CB Scheme 

Nominal voltage UN	
Nominal current IN	
mm <sup>2</sup> /AWG/kcmil	0.2-4



cULus Recognized 

accessories

End cover

D-PT 4-QUATTRO - 3208979



## Feed-through terminal block - PT 4-QUATTRO - 3211797

### accessories

DP PS-6 - 3036738



---

### Partition plate

ATP-ST QUATTRO - 3030815



---

### Screwdriver tools

SZF 1-0,6X3,5 - 1204517



---

### Terminal marking

GBS 5-25X12 - 0810588



ZB 6:UNBEDRUCKT - 1051003



## Feed-through terminal block - PT 4-QUATTRO - 3211797

### accessories

UC-TM 6 - 0818085



UCT-TM 6 - 0828736



ZBF 6:UNBEDRUCKT - 0808710



UC-TMF 6 - 0818140



UCT-TMF 6 - 0828746



TMT 6 R - 0816498





# Feed-through terminal block - PT 4-QUATTRO - 3211797

## accessories

---

TMT (EX9,5)R - 0828295



## Marker carriers

---

GBS-ZB/26X6 - 0809298



CARRIER-TM 300 - 0828282



## Documentation

---

PT-IL - 3208090



## Bridge

---

FBS 2-6 - 3030336



# Feed-through terminal block - PT 4-QUATTRO - 3211797

## accessories

FBS 3-6 - 3030242



FBS 4-6 - 3030255



FBS 5-6 - 3030349



FBS 10-6 - 3030271



FBS 20-6 - 3030365



RB ST (2,5/4)-1,5/S - 3214356



# Feed-through terminal block - PT 4-QUATTRO - 3211797

accessories

---

## Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



## Feed-through terminal block - PT 4-QUATTRO - 3211797

### accessories

NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



# Feed-through terminal block - PT 4-QUATTRO - 3211797

accessories

---

NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



## Feed-through terminal block - PT 4-QUATTRO - 3211797

### accessories

NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



### Labeled terminal marker

ZB 6 CUS - 0824992



UC-TM 6 CUS - 0824589



## Feed-through terminal block - PT 4-QUATTRO - 3211797

accessories

UCT-TM 6 CUS - 0829602



ZBF 6 CUS - 0825027



UC-TMF 6 CUS - 0824646



UCT-TMF 6 CUS - 0829665



TMT 6 R CUS - 0824488



**Test plug terminal block**

## Feed-through terminal block - PT 4-QUATTRO - 3211797

### accessories

MPS-MT - 0201744



PAI-4-FIX-5/6 BU - 3035975



PAI-4-FIX-5/6 OG - 3035974



PAI-4-FIX-5/6 YE - 3035977



PAI-4-FIX-5/6 RD - 3035976



PAI-4-FIX-5/6 GN - 3035978





## Feed-through terminal block - PT 4-QUATTRO - 3211797

### accessories

---

PAI-4-FIX-5/6 BK - 3035980



PAI-4-FIX-5/6 GY - 3035982



PAI-4-FIX-5/6 VT - 3035979



PAI-4-FIX-5/6 BN - 3035981



PS-6 - 3030996



# Feed-through terminal block - PT 4-QUATTRO - 3211797

accessories

PS-6/2,3MM RD - 3038736



---

## Insulating sleeve

MPS-IH WH - 0201663



---

MPS-IH RD - 0201676



---

MPS-IH BU - 0201689



---

MPS-IH YE - 0201692



## Feed-through terminal block - PT 4-QUATTRO - 3211797

### accessories

MPS-IH GN - 0201702



MPS-IH GY - 0201728



MPS-IH BK - 0201731



ISH 4/0,5 - 3002885



ISH 4/1,0 - 3002898



### Planning and marking software

# Feed-through terminal block - PT 4-QUATTRO - 3211797

## accessories

CLIP-PROJECT ADVANCED - 5146040



---

CLIP-PROJECT PROFESSIONAL - 5146053



---

## End block

CLIPFIX 35 - 3022218



---

CLIPFIX 35-5 - 3022276



---

E/NS 35 N - 0800886



---

## Drawings

## Feed-through terminal block - PT 4-QUATTRO - 3211797

Circuit diagram



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>