

Stecker / Steckverteiler mit Isolation

Clips / Raccords mixtes avec isolation

Receptacles / Multi- connectors with insulation

6,3 mm

Werkstoff:
MS sn = Messing verzinkt
Temperaturbeständigkeit:
PVC -10°C bis +75°C
PA -55°C bis +105°C

Matière:
MS sn = laiton étamé
Résistant à une température de:
PVC -10°C à +75°C
PA -55°C à +105°C

Material:
MS sn = tin-plated brass
Temperature range:
PVC -10°C up to +75°C
PA -55°C up to +105°C



Strombelastbarkeit:
0.5 - 1.0 mm² / 10 A max.
1.5 - 2.5 mm² / 15 A max.
4.0 - 6.0 mm² / 25 A max.

Intensité admissible:
0.5 - 1.0 mm² / 10 A max.
1.5 - 2.5 mm² / 15 A max.
4.0 - 6.0 mm² / 25 A max.













Current carrying capacity:
0.5 - 1.0 mm² / 10 A max.
1.5 - 2.5 mm² / 15 A max.
4.0 - 6.0 mm² / 25 A max.

Bestellbeispiel:
Exemple de commande:
Example of order:

3959



UL-No. E235796

Werkstoff Isolation Isolation en Insulation	mm ² (AWG)	für Steckungen pour languettes for tabs	Farben Couleurs Colours	Artikel-Nr. / Numéro d'article / Part-No.		L mm	A mm	øD mm	Stand- Packg	Werkzeuge Outils Tools
				Form A DIN 46245	Form B					
 <p>PA (Nylon)</p>	0.5-1 (22-18)	6.3 x 0.8		3959	3959S	24	-	1.7	500	3974N 3984C 3984D 3984O 3986C 3086N 3986S
	1.5-2.5 (16-14)	6.3 x 0.8		3970	3970S	24	-	2.3	500	
	4-6 (12-10)	6.3 x 0.8			3972S	25	-	3.4	200	
 <p>PVC</p>	0.5-1 (22-18)	6.3 x 0.8		3910	3910S	21.5	10.5	1.7	500	
	1.5-2.5 (16-14)	6.3 x 0.8		3911	3911S	21.5	10.5	2.3	500	
	4-6 (12-10)	6.3 x 0.8		3912	3912S	24	13	3.4	200	
 <p>PVC</p>	0.5-1 (22-18)	6.3 x 0.8		3925	3925S	22.5	10.5	1.7	500	
	1.5-2.5 (16-14)	6.3 x 0.8		3926	3926S	22.5	10.5	2.3	500	
	4-6 (12-10)	6.3 x 0.8		3933	3933S	25	13	3.4	200	

