

Innovative metal and plastic housing design

### Product Description

Housing in plastic or metal version. For power supply in the smallest possible space



### Application range

- Machine and equipment manufacturing
- Control engineering
- Electronic laboratory

### Benefits

- Housing in plastic or metal version. For power supply in the smallest possible space

### Product features

- Cable coupler hood
- 1 lever
- Straight cable entry
- Versions with / without cable gland



Technical Data

Material

Housing: grey thermoplastic, black Lever:  
zinc-plated steel

Protection rating

IP 65 (latched)

Temperature range

-40 °C to +100 °C, short-term up to +125 °C

Article List

Part number	Article	M	PG	Material	Colour	Cable gland	Cable clamping range	Dimensions incl. cable gland	Pieces / PU
10429200	H-A 3 Tgvb		11	Thermoplastic	black				10
10429000	H-A 3 Tgvb		11	Thermoplastic	grey				10
10620300	H-A 3 Tgvb		11	Thermoplastic	black	yes	6,5 - 12	65	10
10429100	H-A 3 Tgvb		11	Thermoplastic	grey	yes	6,5 - 12	65	10
19429200	H-A 3 Tgvb M20	20		Thermoplastic	black				10
19429000	H-A 3 Tgvb M20	20		Thermoplastic	grey				10

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.