

A

B

C

D

E

F

G

H

1

2


3

4

5

6

Maximum Electric Rating: 600V  
 Maximum Electric Current  
 22-16AWG/0.5-1.5mm<sup>2</sup>: 19A  
 16-14AWG/1.5-2.5mm<sup>2</sup>: 27A  
 12-10AWG/4-6mm<sup>2</sup>: 48A  
 Shrinking Temperature:  $\geq 150^{\circ}\text{C}$   
 Operating Temperature:  $-40^{\circ}\text{C} \sim 120^{\circ}\text{C}$   
 Shrinking Ratio: 3:1  
 Terminal Body: Copper  
 Insulation: PE  
 Plating: Tin



Wire Range mm <sup>2</sup> /AWG	Item No.	Stud Size		Dimension (mm)				Insulation Color
		Stud	d2	W	L	D	d1	
0.5~1.5mm <sup>2</sup>	321043SSEL	#8	4.2	6.5	29.5	4.5	1.7	Red
22-16AWG	321053SSEL	#10	5.2	8	28			
1.5~2.5mm <sup>2</sup>	325043SSEL	#8	4.2	6.4	32	5.2	2.3	Blue
16-14AWG	325053SSEL	#10	5.2	8.2	32			
4~6mm <sup>2</sup>	323043SSEL	#8	4.2	8.4	38.7	7	3.5	Yellow
10-12AWG	323053SEL	#10	5.2	9	39.6			

Heat Shrink Spade connector