



Housing design H-B. The industry standard.

Product Description

Ideal for many applications due to a wide range of housings and inserts



Application range

- Plant engineering
- Light & sound technology
- Plastics industry

Benefits

- Ideal for many applications due to a wide range of housings and inserts

Product features

- Hood, low version
- Bolts for double lever
- Side cable entry
- Versions with neck



Technical Data

Material

Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel Sealing: NBR

Protection rating

IP 65 (latched)

Temperature range

-40 °C to +100 °C, short-term up to +125 °C

Article List

Part number	Article	M	PG	Neck	Pieces / PU
H-B housing: hood (side cable entry, bolts for double lever)					
10113000	H-B 24 TS 21		21	yes	5
10123000	H-B 24 TS 29		29	yes	5
19113000	H-B 24 TS M25	25		yes	5
19123000	H-B 24 TS M32	32		yes	5

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.