

Housing design H-B. The industry standard.

Product Description

The smallest housing out of the H-B series. For inserts with high electrical properties



Application range

- Plant engineering
- Control engineering
- Plastics industry

Benefits

- The smallest housing out of the H-B series. For inserts with high electrical properties

Product features

- Hood, low version
- Bolts for single lever
- Straight cable entry
- Versions with / without neck



Technical Data

Material

Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel Sealing: NBR

Protection rating

IP 65 (latched)

Temperature range

-40 °C to +100 °C, short-term up to +125 °C

Article List

| Part number | Article | M | PG | Neck | Pieces / PU |
|--|---------------|----|------|------|-------------|
| H-B housing: hood (straight cable entry, bolts for single lever) | | | | | |
| 10011000 | H-B 6 TG 13,5 | | 13.5 | yes | 10 |
| 10021000 | H-B 6 TG 16 | | 16 | yes | 10 |
| 19011000 | H-B 6 TG M20 | 20 | | | 10 |
| 19021000 | H-B 6 TG M25 | 25 | | | 10 |

Footnote:

Photographs are not to scale and do not represent detailed images of the respective products.