

Circular Connectors C 091 A Female receptacle front mounting, No. of contacts 12, 150 V

Part No. T 3638 000



Series Circular Connectors C091
Subseries Circular Connector C 091 A

Abbildung stellvertretend f r alle verf gbaren Polzahlen.

COMMON CHARACTERISTICS		
No. of contacts		12
Assembly method		front mounting
ELECTRICAL CHARACTERISTICS		
Rated voltage	DIN EN 60664-1 / IEC 60664-1	150V
Rated voltage	UL 1977	60V
Rated impulse voltage	DIN EN 60664-1 / IEC 60664-1	1200V
Installation category	DIN EN 60664-1 / IEC 60664-1	I
Insulation group	DIN EN 60664-1 / IEC 60664-1	II, 400 ≤ CTI < 600
Insulation resistance	DIN EN 60512-2, Test 3a / IEC 60512-2, Test 3a	> 10 ¹⁰ Ω
Contact resistance	DIN EN 60512-2, Test 2a / IEC 60512-2 Test 2a	< 5 mΩ
Pollution degree	DIN EN 60664-1 / IEC 60664-1	1
CLIMATICAL CHARACTERISTICS		
Climatic category	DIN EN 60068-1 / IEC 60068-1	40 / 100 / 56
Temperature range		- 40 °C ... + 100 °C- 40 °F ... + 212 °F
MECHANICAL CHARACTERISTICS		
IP degree of protection	DIN EN 60529 / IEC 60529	IP 40
Insertion and withdrawal force	DIN EN 60512-13-2, Test 13b / IEC 60512-13-2, Test 13b	50 N 180.oz
Mechanical lifetime		≥ 500 mating cycles
MATERIALS		
Insert		Thermoplastic
Contact plating		silver plated
Housing		die cast, nickel plated
FURTHER CHARACTERISTICS		
Termination		solder
Wire gauge		≤ 0,25 mm²
Wire gauge (AWG)		≤ 24
Flammability	UL 94	UL 94 V0
Locking		screw



Circular Connectors C 091 A Female receptacle front mounting, No. of contacts 12, 150 V


Part No. T 3638 000

Series Circular Connectors C091

Subseries Circular Connector C 091 A



Abbildung stellvertretend f r alle verf gbaren Polzahlen.



Ma zeichnung Dimensions in mm (Inch)

Circular Connectors C 091 A Female receptacle front mounting, No. of contacts 12, 150 V


Part No. T 3638 000

Series Circular Connectors C091

Subseries Circular Connector C 091 A



Abbildung stellvertretend f r alle verf gbaren Polzahlen.



Contact arrangement