


PIN HEADER 2,00 mm





ID: 150

STL 12-XXG / STL 22-XXG

Series 500


TECHNICAL DATA

Pitch	2,00 mm
Insulating Material	high temp. thermoplast UL94V-0
Contact Material	copper alloy
Rated Current	1,5 Amp.
Rated Voltage	150 V _{RMS} /V _{DC}
Withstanding Voltage	500 V _{AC} for one minute
Operating Temperature	-40°C to +105°C
Maximum Soldering Temperature	260°C for 10 seconds



for D = 1,5mm

Code	A	B	C
0785	7,85	4,00	2,35
0835	8,35	4,00	2,85
0870	8,70	4,40	2,80
1015	10,15	5,65	3,00
1020	10,20	5,85	2,85
1155	11,55	7,00	3,05
1340	13,40	9,15	2,75
1555	15,55	11,55	2,50
custom			

for D = 2,0mm

Code	A	B	C
0785	7,85	3,50	2,35
0835	8,35	3,50	2,85
0870	8,70	3,90	2,80
1015	10,15	5,15	3,00
1020	10,20	5,35	2,85
1155	11,55	6,50	3,05
1340	13,40	8,65	2,75
1555	15,55	11,05	2,50
custom			

All dimensions in mm.

Other dimensions upon request.

STL XX - XXXX - X,X - G XX - XX U

 XX: 12 = 1 row, pitch 2,00mm
 22 = 2 rows, pitch 2,00mm

Code: see table

 Insulator: 1,5 = insulator height 1,5mm
 2,0 = insulator height 2,0mm

G: Straight contacts

 Plating: TT = Sn
 GT = sel. Au
 GG = Au

 U: RoHS-compliant
 with high temp. plastic

 Poles: 1 row: 2 - 40 contacts possible
 2 rows: 4 - 80 contacts possible