

## Base strip - MC 1,5/ 8-G-3,5 - 1844278

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Header, Nominal current: 8 A, Rated voltage (III/2): 160 V, Number of positions: 8, Pitch: 3.5 mm, Color: green, Contact surface: Tin, Assembly: Soldering

The figure shows a 10-position version of the product

### Product Features

- Versions with engagement noses for locking plugs with self-locking flanges
- Plug-in direction parallel and vertical to the PCB
- Low-profile pin strips with compact pitches
- Individual position coding by inserting coding profiles

### Key commercial data

|                  |               |
|------------------|---------------|
| package_quantity | 100           |
| GTIN             | 4017918113315 |

### Technical data

#### Dimensions

|                |              |
|----------------|--------------|
| Length         | 9.2 mm       |
| Pitch          | 3.5 mm       |
| Dimension a    | 24.5 mm      |
| Pin dimensions | 0,8 x 0,8 mm |
| Hole diameter  | 1.2 mm       |

#### General

|                                  |              |
|----------------------------------|--------------|
| Range of articles                | MC 1,5/...-G |
| Insulating material group        | IIIa         |
| Rated surge voltage (III/3)      | 2.5 kV       |
| Rated surge voltage (III/2)      | 2.5 kV       |
| Rated surge voltage (II/2)       | 2.5 kV       |
| Rated voltage (III/3)            | 160 V        |
| Rated voltage (III/2)            | 160 V        |
| Rated voltage (II/2)             | 250 V        |
| Connection in acc. with standard | EN-VDE       |
| Nominal current $I_N$            | 8 A          |
| Maximum load current             | 8 A          |
| Insulating material              | PBT          |

# Base strip - MC 1,5/ 8-G-3,5 - 1844278

## Technical data

### General

|  |       |
|--|-------|
| <b>Inflammability class according to UL 94</b> | V0    |
| <b>Color</b>                                   | green |
| <b>Number of positions</b>                     | 8     |

## classifications

### eCl@ss

|                   |          |
|-------------------|----------|
| <b>eCl@ss 4.0</b> | 272607xx |
| <b>eCl@ss 4.1</b> | 27260701 |
| <b>eCl@ss 5.0</b> | 27260701 |
| <b>eCl@ss 5.1</b> | 27260701 |
| <b>eCl@ss 6.0</b> | 27260704 |
| <b>eCl@ss 7.0</b> | 27440402 |
| <b>eCl@ss 8.0</b> | 27440402 |

### ETIM

|                 |          |
|-----------------|----------|
| <b>ETIM 3.0</b> | EC001121 |
| <b>ETIM 4.0</b> | EC002637 |
| <b>ETIM 5.0</b> | EC002637 |


### UNSPSC

|                      |          |
|----------------------|----------|
| <b>UNSPSC 6.01</b>   | 30211810 |
| <b>UNSPSC 7.0901</b> | 39121409 |
| <b>UNSPSC 11</b>     | 39121409 |
| <b>UNSPSC 12.01</b>  | 39121409 |
| <b>UNSPSC 13.2</b>   | 39121409 |

## approvals

CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / GOST / IECCE CB Scheme / GOST / CCA / cULus Recognized /

### Approval details

|   |          |          |
|---|----------|----------|
|  |          |          |
| <b>Usegroups</b>  | <b>B</b> | <b>D</b> |
| Nominal voltage UN  | 300 V    | 300 V    |
| Nominal current IN  | 8 A      | 8 A      |
| mm <sup>2</sup> /AWG/kcmil  |          |          |

# Base strip - MC 1,5/ 8-G-3,5 - 1844278

approvals

**UL Recognized**

| Usegroups                  | B     | D     |
|----------------------------|-------|-------|
| Nominal voltage UN         | 300 V | 300 V |
| Nominal current IN         | 8 A   | 8 A   |
| mm <sup>2</sup> /AWG/kcmil |       |       |

**VDE Gutachten mit Fertigungsüberwachung**

|                            |       |
|----------------------------|-------|
| Nominal voltage UN         | 160 V |
| Nominal current IN         | 8 A   |
| mm <sup>2</sup> /AWG/kcmil |       |

**cUL Recognized**

| Usegroups                  | B     | D     |
|----------------------------|-------|-------|
| Nominal voltage UN         | 300 V | 300 V |
| Nominal current IN         | 8 A   | 8 A   |
| mm <sup>2</sup> /AWG/kcmil |       |       |

**GOST**

**IECEE CB Scheme**

|                            |       |
|----------------------------|-------|
| Nominal voltage UN         | 160 V |
| Nominal current IN         | 8 A   |
| mm <sup>2</sup> /AWG/kcmil |       |

**CCA**

|                    |       |
|--------------------|-------|
| Nominal voltage UN | 160 V |
|--------------------|-------|

# Base strip - MC 1,5/ 8-G-3,5 - 1844278

## approvals

|                            |     |
|----------------------------|-----|
| Nominal current IN         | 8 A |
| mm <sup>2</sup> /AWG/kcmil |     |



## accessories

### Labeled terminal marker

SK 3,5/2,8:FORTL.ZAHLEN - 0804073



---

### Coding element

CP-MSTB - 1734634



---

## accessories

MC 1,5/10-LWL 1,5-3,5 - 1841161



MC 1,5/10-LWL 2,3-3,5 - 1841187



# Base strip - MC 1,5/ 8-G-3,5 - 1844278

accessories


MC 1,5/10-LWL 4-3,5 - 1841200



## Drawings

Drilling diagram


Diagram



# Base strip - MC 1,5/ 8-G-3,5 - 1844278


Diagram

Plug: MCVR(W) 1,5/5-ST(F)-3,81(3,5)  
Header: MC(V) 1,5/5-G(F)-3,81(3,5)



Diagram


Plug: MC 1,5/5-ST(F)-3,81(3,5)  
Header: MC(V) 1,5/5-G(F)-3,81(3,5)




# Base strip - MC 1,5/ 8-G-3,5 - 1844278

Diagram

Plug: FRONT-MC 1,5/5-ST(F)-3,81(3,5)  
 Header: MC(V) 1,5/5-G(F)-3,81(3,5)



Diagram




Type: TFMC 1,5/...-ST-3,5 with MC 1,5/...-G-3,5

Diagram

Type: MC 1,5/...-ST-3,5 with MC 1,5/...-G-3,5

# Base strip - MC 1,5/ 8-G-3,5 - 1844278

Dimensioned drawing



© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>