



Shellsize	A	B	C	ØD	E	F	G <sup>+1</sup> <sub>-3</sub>	Cable ø	Part-NO.
1	40.76	25.0	SW 22	24.6	51.0	22.0	77.0	5 - 10	<b>165X14869X</b>
2	49.06	33.3	SW 24	26.5	51.0	22.0	79.0	6 - 12	<b>165X14879X</b>
3	62.80	47.04	SW 24	26.5	59.5	22.0	87.5	6 - 12	<b>165X14889X</b>
4	78.86	63.5	SW 33	36.2	67.0	22.0	99.0	9 - 16	<b>165X14899X</b>
5	76.46	61.1	SW 42	47.0	67.0	24.8	107.0	13 - 20	<b>165X14909X</b>



- NOTES:**
- HOOD: PBT GF; BLACK
  - SCREWS: STAINLESS STEEL

APPROVAL \* FREIGABE \* DEBLOCAGE \* AUTORIZACION \* APPROVAL

CUSTOMER APPROVAL DATE:

NAME: TITLE:

COMPANY NAME:

APPROVAL \* FREIGABE \* DEBLOCAGE \* AUTORIZACION \* APPROVAL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY, WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance dim. in mm

2004	date	name
drawn	25.11.	Lehmenkühler
appd.	25.11.	Mickenbecker
norm		
d-old		

**CONEC**

scale: 1:1

material: SEE NOTES

title: **WATER RESISTANT D-SUB HOOD**  
9-50pos.  
with short screw

dwg no: AutoCAD 2004 DIN-A  
16K1A1289 3  
sh: 1/1

part no: SEE TABLE