

Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Quick connection, Cross section: 0.25 mm² - 1.5 mm², AWG: 24 - 16, Width: 5.2 mm, Color: gray, Mounting type: NS 35/7,5, NS 35/7,5

Product Features

- Compact design
- Tested for railway applications



Key commercial data

package_quantity	50
GTIN	4017918932497

Technical data

General

Note	The max. load current must not be exceeded by the total current of all connected conductors.
Number of levels	1
Number of connections	4
Color	gray
Insulating material	PA
Inflammability class according to UL 94	V0
Area of application	Railway industry
Area of application	Mechanical engineering
Area of application	Plant engineering
Area of application	Process industry

General

Maximum load current	17.5 A (with 1.5 mm ² conductor cross section)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1

Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

Technical data

General

Nominal current I_N	17.5 A (the maximum load current must not be exceeded by the total current of all connected conductors)
Nominal voltage U_N	800 V
Open side panel	ja

Dimensions

Width	5.2 mm
Length	94 mm
Height NS 35/7,5	39.3 mm
Height NS 35/15	46.8 mm

Connection data

Conductor cross section solid min.	0.25 mm ²
Conductor cross section solid max.	1.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	16
Conductor cross section stranded min.	0.25 mm ²
Conductor cross section stranded max.	1.5 mm ²
Min. AWG conductor cross section, stranded	24
Max. AWG conductor cross section, stranded	16
Connection method	Quick connection
Material wire insulation	PVC / PE
Structure of individual litz in acc. with VDE 0295 / smallest wire diameter	VDE 0295 Cl.1-5

classifications

eCl@ss

eCl@ss 4.0	27141130
eCl@ss 4.1	27141130
eCl@ss 5.0	27141130
eCl@ss 5.1	27141130
eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
--------------------	----------

Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

classifications

UNSPSC

UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

IECEX / ATEX / CSA / UL Recognized / cUL Recognized / GOST / LR / GL / BV / DNV / ABS / KR / NK / GOST / cULus Recognized /

Approval details

IECEX	
Nominal voltage UN	550 V
Nominal current IN	16 A
mm ² /AWG/kcmil	0.25-1.5

ATEX	
Nominal voltage UN	550 V
Nominal current IN	16 A
mm ² /AWG/kcmil	0.25-1.5

CSA		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	10 A	10 A
mm ² /AWG/kcmil	24-16	24-16

UL Recognized		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	10 A	10 A
mm ² /AWG/kcmil	24-16	24-16

Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

approvals

cUL Recognized		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	10 A	10 A
mm ² /AWG/kcmil	24-16	24-16

GOST

LR

GL

BV

DNV

ABS

KR

NK

--

cULus Recognized

accessories

End cover

Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

accessories

D-QTC 1,5-QUATTRO - 3205174



DS-QTC 1,5 - 3205200



DP PS-5 - 3036725



Test plug terminal block

PS-4/E - 3036709



PAI-4-FIX-5/6 BU - 3035975



Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

accessories

PAI-4-FIX-5/6 OG - 3035974



PAI-4-FIX-5/6 YE - 3035977



PAI-4-FIX-5/6 RD - 3035976



PAI-4-FIX-5/6 GN - 3035978



PAI-4-FIX-5/6 BK - 3035980



PAI-4-FIX-5/6 GY - 3035982



Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

accessories

PAI-4-FIX-5/6 VT - 3035979



PAI-4-FIX-5/6 BN - 3035981



PS-5 - 3030983



PS-5/2,3MM RD - 3038723



Screwdriver tools

SZF 1-0,6X3,5 - 1204517



Documentation

Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

accessories

QTC-IL - 3039926



Bridge

FBS 2-5 - 3030161



FBS 3-5 - 3030174



FBS 4-5 - 3030187



FBS 5-5 - 3030190



Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

accessories

FBS 10-5 - 3030213



FBS 20-5 - 3030226



RB ST (2,5/4)-1,5 - 3038943



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

accessories

NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

accessories

NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



NS 35/15 WH UNPERF 2000MM - 1204135



Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

accessories

NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



NS 35/15-2,3 UNPERF 2000MM - 1201798



Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

accessories

Terminal marking

ZB 5 : UNBEDRUCKT - 1050004



UC-TM 5 - 0818108



UCT-TM 5 - 0828734



ZBF 5: UNBEDRUCKT - 0808642



UC-TMF 5 - 0818153



Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

accessories

UCT-TMF 5 - 0828744



Labeled terminal marker

ZB 5 CUS - 0824962



UC-TM 5 CUS - 0824581



UCT-TM 5 CUS - 0829595



ZBF 5 CUS - 0825025



Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

accessories

UC-TMF 5 CUS - 0824638



UCT-TMF 5 CUS - 0829658



End block

CLIPFIX 35 - 3022218



CLIPFIX 35-5 - 3022276



E/NS 35 N - 0800886



Drawings

Feed-through terminal block - QTC 1,5-QUATTRO - 3205077

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>