

1	2		3	4	5	6	7	8				
ISS			ZONE			REVISIONS						
DESCRIPTION			PER REQUEST			DATE						
<p>NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)</p> <p>1. BRASS PER QQ-B-626</p> <p>2. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE</p> <p>3. PHOSPHOR BRONZE PER QQ-B-750</p> <p>4. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE</p> <p>5. JIS H 3250, C 2700</p>												
<p>RECOMMENDED CABLE STRIPPING DIM'S</p>				<p>M8XP0.75-6g</p> <p>8 HEX</p>								
				<p>1. CRIMPED FERRULE HEX CRIMP SIZE .213"</p> <p>2. CRIMPED CONTACT PIN HEX CRIMP SIZE .068"</p>								
5	FERRULE	NOTE 5	NOTE 2	1	FR-64/54X127	DIMENSIONS ARE IN MILLIMETERS			PART NO.	FME6121B1-ND3G-1-50		<h1 style="text-align: center;">Amphenol</h1> <p style="text-align: center;">TITLE FME ROTATING NIPPLE</p> <p style="text-align: center;">DRAWING NO. KJ-FME6121B1-ND3G-58CU-50</p> <p style="text-align: center;">ITEM NO.</p>
4	HEX NUT	NOTE 1	NOTE 2	1	FME6121A1-4-8/62	UNLESS OTHERWISE SPECIFIED TOLERANCES			APPROVED	DATE	10-11-01'	
3	CONTACT PIN	NOTE 3	NOTE 4	1	FME6121B1-3-21/11	0.5-6 = ±0.2			CHECKED	DATE	10-11-01'	
2	INSULATOR	DELTRIN	NATURAL	1	FME6121B1-2-50-B	6-30 = ±0.4			DRAWN	DATE	10-11-01'	
1	BODY	NOTE 1	NOTE 2	1	FME6121A1-1-46/31	30-120 = ±0.6						
						120-315 = ±1						
						315-1000 = ±1.6						
						1000-2000 = ±2.4						
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.	SCALE	3/1	ISSUE	A	FILE NO.		
1	2		3	4	5	6	7	8				