

Plug-in card block - SKBI 32/F/ZB - 2261096

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Plug-in card block, Nominal current: 4 A, Number of positions: 32, Pitch: 5.08 mm, Connection method: Screw connection

Key commercial data

package_quantity	1
GTIN	4017918053833

Technical data

Dimensions

Length	43 mm
Height	138 mm
Width	112 mm
Pitch	5.08 mm
Hole diameter	4.2 mm

General

Range of articles	SKBI 32
Connection in acc. with standard	EN-VDE
Nominal current I_N	4 A
Nominal voltage U_N	250 V (in acc. with DIN VDE 0110/Gr.B)
Nominal cross section	2.5 mm ²
Stripping length	8 mm
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm
Number of positions	32

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

Plug-in card block - SKBI 32/F/ZB - 2261096

classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260710
eCl@ss 7.0	27141152
eCl@ss 8.0	27141152

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002642
ETIM 5.0	EC002780

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

approvals

GOST / GOST /

Approval details




accessories

SF-SKBI 31/32 - 2261009

Plug-in card block - SKBI 32/F/ZB - 2261096


Drawings

Dimensioned drawing



Plug-in card block - SKBI 32/F/ZB - 2261096

Schematic diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>