








Notes:

- Electrical Specifications:
 - Meets EIA/TIA-568-B.2 Cat.5e Specification
 - Contact Resistance: 20mOhm max.
 - Insulation Resistance: 500MOhm min. @ 100 VDC
 - Current Rating: 1.2A max. at 25°C
 - Working Voltage: 100 VDC
 - DWV: 1000 VDC/60s Contact to Contact, 1500 VDC/60s Contact to Metal Shell
 - Operating Temperature: -40°C to +85°C
- Material and Finish:
 - Thread Coupling Ring and Housing: Polyester (Black) or Metallized ABS, UL94 V-0 (Nickel Plated)
 - Cable Fitting: PA (Black), UL94 V-0 or Brass, Nickel Plated
 - Cable Fitting Rubber Ring: NBR, Color: Black
 - RJ45 Plug Metal Shell: Copper Alloy, Nickel Plated
 - RJ45 Plug Plastic Housing: Clear Polycarbonate UL94 V-0
 - RJ45 Plug Contacts: Phosphor Bronze, Finish: 50u" Gold min. over Nickel
- RJ45 Plug accepts both Stranded and Solid Cables with Outer Diameter of 4.83mm to 6.73mm
- Plastic Version Cable Fitting accepts Cable Outer Diameter Range of 4mm to 8mm
- Metal Version Cable Gland accepts Cable Outer Diameter Range of 4.5mm to 8mm
- RoHS compliant

Directive 2002/95/EC
"RoHS"
Compliant

Version	"A"	Part Number
Plastic Version	18.9mm REF.	17-100464
Metallized Plastic Version	17.9mm REF.	17-100474

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION OF CONEC CORPORATION DOT NOT ALTER CAD DRAWING BY HAND	Customer:			Tolerance Unless otherwise specified 0 PLC ±0.50 1 PLC ±0.38 2 PLC ±0.25 3 PLC ±0.10 ANGLES ±3°		Scale: 1.5:1		Dim. in mm		
	Name		Title			Approval Date	Autodesk Inventor		Material: See Notes	
				2007	Date	Name	Title: RJ45 Cable Strain Relief Kit Industrial Ethernet Connector with shielded Cat. 5e RJ45 Plug			
				Draw.	Dec. 03	Vincent Ke				
				Appd.	Dec. 03	J. Chaudry				
				Norm						
					D-old		Drawing No.: 39K1A365			DIN A3
	a	origin				Part No.: SEE P/N ABOVE			Sheet 1/1	
Rev.	Changes	Date	Name							