

1

2

3




4

5

6

7

Signature	Revision History	Date	Rev.
Norman Xu	For Bulk Production	Dec.20,2005	01



PIN OUT		
DB 9PIN (M)		DB 25PIN (M)
1	_____	8
2	_____	3
3	_____	2
4	_____	20
5	_____	7
6	_____	6
7	_____	4
8	_____	5
9	_____	22
SHELL	_____	SHELL

NOTES:

- VOLTAGE RATING:300 VAC(rms)
- CURRENT RATING: 3 Amp CONTINUOUS
- DIELECTRIC STRENGTH: 500 VAC
- CONTACT RESISTANCE: 10m OHM MAX 1 ADC
- INSULATION RESISTANCE: 500M OHM MIN
- MATING FORCE INSERTION FORCE: 1 OZ-16 OZ  
AVERAGE 150 GRAM  
EXTRACTION FORCE: 1 KG MIN

MATERIALS:

- HOUSING:THERMOPLASTIC , P.B.T.  
UL94V-0 , BLACK
- CONTACT: PHOSPHOR BRONZE GOLD  
SELECTIVE PLATED OVER NICKEL
- SHELL: STEEL TIN PLATED
- PACKING:SEE P-0039 REV.C PACKING DRAWING+EAN CODE  
EAN CODE:4016032059943
- LABEL:ORANGE COLOR WITH WHITE CHARACTOR

RoHS Compliant

Drawn by Dec.20,2005 Norman Xu  Checked by Dec.20,2005 Alex Dan  Approved by	Date	Name	Part No.  <b>AB 468</b>
	Title. <b>DB9M to DB25F adapter</b>		
	<b>ASSMANN</b> Electronic GmbH		Scale N/A Unit MM Sheet 1/1

ST81407

1

2

3

4

5

6

7